

## ACCESORIOS DE COMPROBACIÓN DE CALIBRACIÓN PARA MEDIDORES GAUSS MODELO 25



SKU: N / A | Categorías: [Magnetómetros](#) |

## DESCRIPCIÓN DEL PRODUCTO

[vc\_row type="in\_container" full\_screen\_row\_position="middle" column\_margin="default" scene\_position="center" text\_color="dark" text\_align="left" overlay\_strength="0.3" shape\_divider\_position="bottom" bg\_image\_animation="none"][vc\_column column\_padding="no-extra-padding" column\_padding\_position="all" background\_color\_opacity="1" background\_hover\_color\_opacity="1" column\_link\_target="\_self" column\_shadow="none" column\_border\_radius="none" width="1/1" tablet\_width\_inherit="default" tablet\_text\_alignment="default" phone\_text\_alignment="default" overlay\_strength="0.3" column\_border\_width="none" column\_border\_style="solid" bg\_image\_animation="none"]**Accesorios de Comprobación de Calibración para Medidores Gauss**

### Modelo 25

[/vc\_column\_text][vc\_column][vc\_row][vc\_row type="in\_container" full\_screen\_row\_position="middle" column\_margin="default" scene\_position="center" text\_color="dark" text\_align="left" overlay\_strength="0.3" shape\_divider\_position="bottom" bg\_image\_animation="none"][vc\_column column\_padding="no-extra-padding" column\_padding\_position="all" background\_color\_opacity="1" background\_hover\_color\_opacity="1" column\_link\_target="\_self" column\_shadow="none" column\_border\_radius="none" width="1/1" tablet\_width\_inherit="default" tablet\_text\_alignment="default" phone\_text\_alignment="default" overlay\_strength="0.3" column\_border\_width="none" column\_border\_style="solid" bg\_image\_animation="none"]**Descripción del Producto**

Estos dispositivos de verificación se utilizan para determinar la precisión de calibración de los magnetómetros de bolsillo Annis Modelo 25.[/vc\_column\_text][/vc\_column][/vc\_row]

## INFORMACIÓN ADICIONAL

COTECNO