

APARATOS ELÉCTRICOS



SKU: N / A | **Categorías:** [Humedad](#), [Thies Klima](#) |

DESCRIPCIÓN DEL PRODUCTO

[vc_row type="in_container" full_screen_row_position="middle" column_margin="default" scene_position="center" text_color="dark" text_align="left" overlay_strength="0.3" shape_divider_position="bottom" bg_image_animation="none"] [vc_column column_padding="no-extra-padding" column_padding_position="all" background_color_opacity="1" background_hover_color_opacity="1" column_link_target="_self" column_shadow="none" column_border_radius="none" width="1/1" tablet_width_inherit="default" tablet_text_alignment="default" phone_text_alignment="default" overlay_strength="0.3" column_border_width="none" column_border_style="solid" bg_image_animation="none"] [vc_column_text] Los sensores de humedad eléctricos miden la humedad relativa del aire, generalmente mediante un elemento de medición que cambia la capacidad eléctrica proporcionalmente a la humedad del aire. La señal de medición siempre se prepara y se emite a través de una señal estándar analógica o a través de una interfaz digital en serie con protocolo MODBUS, por ejemplo. Los sensores para la medición de la humedad relativa del aire a menudo se combinan con sensores de temperatura en un solo instrumento. [/vc_column_text] [/vc_row_inner column_margin="default" text_align="left" css=".vc_custom_1597668708409{border-radius: 2px !important;}"] [vc_column_inner column_padding="no-extra-padding" column_padding_position="all" background_color="#9492ff" background_color_opacity="1" background_hover_color_opacity="1" font_color="ffffff" column_shadow="none" column_border_radius="none" column_link_target="_self" width="1/4" tablet_width_inherit="default" overlay_strength="0.3" column_border_width="none" column_border_style="solid" bg_image_animation="none"] [vc_column_text]

Imagen

[/vc_column_text] [/vc_column_inner] [vc_column_inner column_padding="no-extra-padding" column_padding_position="all" background_color="#9492ff" background_color_opacity="1" background_hover_color_opacity="1" font_color="ffffff" column_shadow="none" column_border_radius="none" column_link_target="_self" width="1/4" tablet_width_inherit="default" overlay_strength="0.3" column_border_width="none" column_border_style="solid" bg_image_animation="none"] [vc_column_text]

Nombre del Producto

[/vc_column_text] [/vc_column_inner] [vc_column_inner column_padding="no-extra-padding" column_padding_position="all" background_color="#9492ff" background_color_opacity="1" background_hover_color_opacity="1" font_color="ffffff" column_shadow="none" column_border_radius="none" column_link_target="_self" width="1/2" tablet_width_inherit="default" overlay_strength="0.3" column_border_width="none" column_border_style="solid" bg_image_animation="none"] [vc_column_text]

Descripción corta

[/vc_column_text] [/vc_column_inner] [/vc_row_inner]

[vc_row_inner column_margin="default" text_align="left"] [vc_column_inner column_padding="no-extra-padding" column_padding_position="all" background_color_opacity="1" background_hover_color_opacity="1" column_shadow="none" column_border_radius="none" column_link_target="_self" width="1/4" tablet_width_inherit="default" overlay_strength="0.3" column_border_width="none" column_border_style="solid" bg_image_animation="none"] [image_with_animation image_url="136646" alignment="center" animation="Fade In" hover_animation="none" border_radius="none" box_shadow="none" image_loading="default" max_width="100%" max_width_mobile="default"] [/vc_column_inner] [vc_column_inner column_padding="no-extra-padding" column_padding_position="all" background_color_opacity="1" background_hover_color_opacity="1" column_shadow="none" column_border_radius="none" column_link_target="_self" width="1/4" tablet_width_inherit="default" overlay_strength="0.3" column_border_width="none" column_border_style="solid" bg_image_animation="none"] [vc_column_text]

Hygro-Transmisor

1.1000.50.xxx[/vc_column_text][vc_column_inner][vc_column_inner column_padding="no-extra-padding" column_padding_position="all" background_color_opacity="1" background_hover_color_opacity="1" column_shadow="none" column_border_radius="none" column_link_target="_self" width="1/2" tablet_width_inherit="default" overlay_strength="0.3" column_border_width="none" column_border_style="solid" bg_image_animation="none"][/vc_column_text]Mide e indica la humedad. Equipado con salida eléctrica para transmisión de largo alcance. Construcción robusta. Las partes expuestas, como el cabezal de la caja y el vástago de inmersión, están hechas de acero inoxidable.[/vc_column_text][nectar_cta btn_style="see-through" heading_tag="h6" button_color="default" link_type="new_tab" alignment="left" display="block" link_text="Leer más" url="http://test.cotecno.cl/nuestros-productos/hygro-transmisor/"][/vc_column_inner][vc_row_inner]

[vc_row_inner column_margin="default" text_align="left"][vc_column_inner column_padding="no-extra-padding" column_padding_position="all" background_color_opacity="1" background_hover_color_opacity="1" column_shadow="none" column_border_radius="none" column_link_target="_self" width="1/4" tablet_width_inherit="default" overlay_strength="0.3" column_border_width="none" column_border_style="solid" bg_image_animation="none"][image_with_animation image_url="136713" alignment="center" animation="Fade In" hover_animation="none" border_radius="none" box_shadow="none" image_loading="default" max_width="100%" max_width_mobile="default"][/vc_column_inner][vc_column_inner column_padding="no-extra-padding" column_padding_position="all" background_color_opacity="1" background_hover_color_opacity="1" column_shadow="none" column_border_radius="none" column_link_target="_self" width="1/4" tablet_width_inherit="default" overlay_strength="0.3" column_border_width="none" column_border_style="solid" bg_image_animation="none"][/vc_column_text]

Transmisor Psychro

1.1130.xx.000

[/vc_column_text][vc_column_inner][vc_column_inner column_padding="no-extra-padding" column_padding_position="all" background_color_opacity="1" background_hover_color_opacity="1" column_shadow="none" column_border_radius="none" column_link_target="_self" width="1/2" tablet_width_inherit="default" overlay_strength="0.3" column_border_width="none" column_border_style="solid" bg_image_animation="none"][/vc_column_text]Instrumento de medición para determinar los valores de humedad del aire en función de la temperatura seca y húmeda. Un recipiente de agua adjunto permite humedecer el psicro sensor. Los tubos de protección de doble pared protegen el sensor de la radiación. Una percha, incluida en la entrega, sirve para el montaje lateral del psicro-transmisor en una fachada, pared, etc.[/vc_column_text][nectar_cta btn_style="see-through" heading_tag="h6" button_color="default" link_type="new_tab" alignment="left" display="block" link_text="Leer más" url="http://test.cotecno.cl/nuestros-productos/transmisor-psychro/"][/vc_column_inner][vc_row_inner]

[vc_row_inner column_margin="default" text_align="left"][vc_column_inner column_padding="no-extra-padding" column_padding_position="all" background_color_opacity="1" background_hover_color_opacity="1" column_shadow="none" column_border_radius="none" column_link_target="_self" width="1/4" tablet_width_inherit="default" overlay_strength="0.3" column_border_width="none" column_border_style="solid" bg_image_animation="none"][image_with_animation image_url="138426" alignment="center" animation="Fade In" hover_animation="none" border_radius="none" box_shadow="none" image_loading="default" max_width="100%" max_width_mobile="default"][/vc_column_inner][vc_column_inner column_padding="no-extra-padding" column_padding_position="all" background_color_opacity="1" background_hover_color_opacity="1" column_shadow="none" column_border_radius="none" column_link_target="_self" width="1/4" tablet_width_inherit="default" overlay_strength="0.3" column_border_width="none" column_border_style="solid" bg_image_animation="none"][/vc_column_text]

Sonda De Humedad Del Suelo Trime-Pico 32

```
1.0231.00.xxx[/vc_column_text][vc_column_inner][vc_column_inner column_padding="no-extra-padding"
column_padding_position="all" background_color_opacity="1" background_hover_color_opacity="1"
column_shadow="none" column_border_radius="none" column_link_target="_self" width="1/2"
tablet_width_inherit="default" overlay_strength="0.3" column_border_width="none" column_border_style="solid"
bg_image_animation="none"]vc_column_textSensor de humedad del suelo con sensor de temperatura
integrado.[/vc_column_text][nectar_cta btn_style="see-through" heading_tag="h6" button_color="default"
link_type="new_tab" alignment="left" display="block" link_text="Leer más"
url="http://test.cotecno.cl/nuestros-productos/sonda-de-humedad-del-suelo-trime-pico-32/"][/vc_column_inner][vc_row_inne
r]
```

```
[vc_row_inner column_margin="default" text_align="left"][vc_column_inner column_padding="no-extra-padding"
column_padding_position="all" background_color_opacity="1" background_hover_color_opacity="1"
column_shadow="none" column_border_radius="none" column_link_target="_self" width="1/4"
tablet_width_inherit="default" overlay_strength="0.3" column_border_width="none" column_border_style="solid"
bg_image_animation="none"][image_with_animation image_url="136646" alignment="center" animation="Fade In"
hover_animation="none" border_radius="none" box_shadow="none" image_loading="default" max_width="100%"
max_width_mobile="default"][/vc_column_inner][vc_column_inner column_padding="no-extra-padding"
column_padding_position="all" background_color_opacity="1" background_hover_color_opacity="1"
column_shadow="none" column_border_radius="none" column_link_target="_self" width="1/4"
tablet_width_inherit="default" overlay_strength="0.3" column_border_width="none" column_border_style="solid"
bg_image_animation="none"]vc_column_text]
```

Transmisor Hygro-Thermo

```
1.1005.50.xxx[/vc_column_text][vc_column_inner][vc_column_inner column_padding="no-extra-padding"
column_padding_position="all" background_color_opacity="1" background_hover_color_opacity="1"
column_shadow="none" column_border_radius="none" column_link_target="_self" width="1/2"
tablet_width_inherit="default" overlay_strength="0.3" column_border_width="none" column_border_style="solid"
bg_image_animation="none"]vc_column_textInstrumento diseñado para medir la temperatura y la humedad del
aire.[/vc_column_text][nectar_cta btn_style="see-through" heading_tag="h6" button_color="default" link_type="new_tab"
alignment="left" display="block" link_text="Leer más"
url="http://test.cotecno.cl/nuestros-productos/transmisor-hygro-thermo/"][/vc_column_inner][vc_row_inner]
```

```
[vc_row_inner column_margin="default" text_align="left"][vc_column_inner column_padding="no-extra-padding"
column_padding_position="all" background_color_opacity="1" background_hover_color_opacity="1"
column_shadow="none" column_border_radius="none" column_link_target="_self" width="1/4"
tablet_width_inherit="default" overlay_strength="0.3" column_border_width="none" column_border_style="solid"
bg_image_animation="none"][image_with_animation image_url="136647" alignment="center" animation="Fade In"
hover_animation="none" border_radius="none" box_shadow="none" image_loading="default" max_width="100%"
max_width_mobile="default"][/vc_column_inner][vc_column_inner column_padding="no-extra-padding"
column_padding_position="all" background_color_opacity="1" background_hover_color_opacity="1"
column_shadow="none" column_border_radius="none" column_link_target="_self" width="1/4"
tablet_width_inherit="default" overlay_strength="0.3" column_border_width="none" column_border_style="solid"
bg_image_animation="none"]vc_column_text]
```

Transmisor Hygro-Thermo Compacto

```
1.1005.54.1xx[/vc_column_text][vc_column_inner][vc_column_inner column_padding="no-extra-padding"
column_padding_position="all" background_color_opacity="1" background_hover_color_opacity="1"
column_shadow="none" column border radius="none" column link target=" self" width="1/2"
```

tablet_width_inherit="default" overlay_strength="0.3" column_border_width="none" column_border_style="solid" bg_image_animation="none"]

[vc_column_text]Instrumento diseñado para medir la temperatura y la humedad del aire.

- Salidas analógicas

[vc_column_text][nectar_cta btn_style="see-through" heading_tag="h6" button_color="default" link_type="new_tab" alignment="left" display="block" link_text="Leer más" url="http://test.cotecno.cl/nuestros-productos/transmisor-hygro-thermo-compacto/"]

[vc_column_inner][vc_row_inner]

[vc_row_inner column_margin="default" text_align="left"]

[vc_column_inner column_padding="no-extra-padding" column_padding_position="all" background_color_opacity="1" background_hover_color_opacity="1" column_shadow="none" column_border_radius="none" column_link_target="_self" width="1/4" tablet_width_inherit="default" overlay_strength="0.3" column_border_width="none" column_border_style="solid" bg_image_animation="none"]

[image_with_animation image_url="136648" alignment="center" animation="Fade In" hover_animation="none" border_radius="none" box_shadow="none" image_loading="default" max_width="100%" max_width_mobile="default"]

[vc_column_inner][vc_column_inner column_padding="no-extra-padding" column_padding_position="all" background_color_opacity="1" background_hover_color_opacity="1" column_shadow="none" column_border_radius="none" column_link_target="_self" width="1/4" tablet_width_inherit="default" overlay_strength="0.3" column_border_width="none" column_border_style="solid" bg_image_animation="none"]

[vc_column_text]

Transmisor Hygro-Thermo Compacto

1.1005.54.7xx

[vc_column_text][vc_column_inner][vc_column_inner column_padding="no-extra-padding" column_padding_position="all" background_color_opacity="1" background_hover_color_opacity="1" column_shadow="none" column_border_radius="none" column_link_target="_self" width="1/2" tablet_width_inherit="default" overlay_strength="0.3" column_border_width="none" column_border_style="solid" bg_image_animation="none"]

[vc_column_text]Instrumento diseñado para medir la temperatura y la humedad del aire. Con conexión de enchufe.

- Salidas analógicas
- Conexión de enchufe

[vc_column_text][nectar_cta btn_style="see-through" heading_tag="h6" button_color="default" link_type="new_tab" alignment="left" display="block" link_text="Leer más" url="http://test.cotecno.cl/nuestros-productos/thies-clima-transmisor-hygro-thermo-compacto/"]

[vc_column_inner][vc_row_inner]

[vc_row_inner column_margin="default" text_align="left"]

[vc_column_inner column_padding="no-extra-padding" column_padding_position="all" background_color_opacity="1" background_hover_color_opacity="1" column_shadow="none" column_border_radius="none" column_link_target="_self" width="1/4" tablet_width_inherit="default" overlay_strength="0.3" column_border_width="none" column_border_style="solid" bg_image_animation="none"]

[image_with_animation image_url="136648" alignment="center" animation="Fade In" hover_animation="none" border_radius="none" box_shadow="none" image_loading="default" max_width="100%" max_width_mobile="default"]

[vc_column_inner][vc_column_inner column_padding="no-extra-padding" column_padding_position="all" background_color_opacity="1" background_hover_color_opacity="1" column_shadow="none" column_border_radius="none" column_link_target="_self" width="1/4" tablet_width_inherit="default" overlay_strength="0.3" column_border_width="none" column_border_style="solid" bg_image_animation="none"]

[vc_column_text]

Transmisor Hygro-Thermo Compacto

1.1005.54.780

[vc_column_text][vc_column_inner][vc_column_inner column_padding="no-extra-padding" column_padding_position="all" background_color_opacity="1" background_hover_color_opacity="1"

column_shadow="none" column_border_radius="none" column_link_target="_self" width="1/2"
tablet_width_inherit="default" overlay_strength="0.3" column_border_width="none" column_border_style="solid"
bg_image_animation="none"] [vc_column_text] Instrumento diseñado para medir la temperatura y la humedad del aire.

- Interfaz MODBUS RTU
- Conexión de enchufe

[/vc_column_text] [nectar_cta btn_style="see-through" heading_tag="h6" button_color="default" link_type="new_tab"
alignment="left" display="block" link_text="Leer más"
url="http://test.cotecno.cl/nuestros-productos/thies-transmisor-hygro-thermo-compacto/"] [/vc_column_inner] [/vc_row_inner]

[vc_row_inner column_margin="default" text_align="left"] [vc_column_inner column_padding="no-extra-padding"
column_padding_position="all" background_color_opacity="1" background_hover_color_opacity="1"
column_shadow="none" column_border_radius="none" column_link_target="_self" width="1/4"
tablet_width_inherit="default" overlay_strength="0.3" column_border_width="none" column_border_style="solid"
bg_image_animation="none"] [image_with_animation image_url="136653" alignment="center" animation="Fade In"
hover_animation="none" border_radius="none" box_shadow="none" image_loading="default" max_width="100%"
max_width_mobile="default"] [/vc_column_inner] [vc_column_inner column_padding="no-extra-padding"
column_padding_position="all" background_color_opacity="1" background_hover_color_opacity="1"
column_shadow="none" column_border_radius="none" column_link_target="_self" width="1/4"
tablet_width_inherit="default" overlay_strength="0.3" column_border_width="none" column_border_style="solid"
bg_image_animation="none"] [vc_column_text]

Sensor De Clima EE.UU

4.920x.x0.00x [vc_column_text] [/vc_column_inner] [vc_column_inner column_padding="no-extra-padding"
column_padding_position="all" background_color_opacity="1" background_hover_color_opacity="1"
column_shadow="none" column_border_radius="none" column_link_target="_self" width="1/2"
tablet_width_inherit="default" overlay_strength="0.3" column_border_width="none" column_border_style="solid"
bg_image_animation="none"] [vc_column_text] El CLIMA SENSOR US sirve para la medición de parámetros ambientales.
Estos están disponibles para su posterior procesamiento como

- Telegrama en serie a través de RS485 / 422
y / o como
- Señales analógicas mediante salidas de tensión

[/vc_column_text] [nectar_cta btn_style="see-through" heading_tag="h6" button_color="default" link_type="new_tab"
alignment="left" display="block" link_text="Leer más"
url="http://test.cotecno.cl/nuestros-productos/sensor-de-clima-us/"] [/vc_column_inner] [/vc_row_inner]

[/vc_column] [/vc_row]

INFORMACIÓN ADICIONAL

COTECNO