

BROCAS DE LA MARCA LIGHTNING



Características:

Brocas penetrantes de perforación rápida para realizar el trabajo rápidamente

Lightning Brand Core Bits son nuestras brocas de perforación de penetración más rápidas. Brocas de diamante de larga duración y alta calidad fabricadas según los estándares de la Asociación de Aserrado y Perforación (CSDA).

Nueva forma de segmento agresivo

Forma trapezoidal = Perforación más rápida

- Diseñado para aplicaciones de búsqueda y rescate
- Concreto reforzado
- Hormigón
- Hormigón pretensado
- Materiales superduros y cerámicos
- Asfalto / macadán
- Matriz de diamante diseñada a medida
- Diamantes seleccionados de alta calidad, ubicados en una matriz metálica resistente y unidos a tubos de acero pesado
- Diámetros de broca estándar de 1 "a 3"
- Muestra de núcleo de longitud de bits estándar de 13 "y longitudes personalizadas diseñadas para aplicaciones especiales de perforación
- Perforación rentable con velocidad de penetración máxima con extremos cerrados

SKU: N / A | **Categorías:** [Broca](#) |

COTECNO

VARIACIONES





Imagen	SKU	Descripción	SKU / Modelo
 <p>Core Drill Bits KO</p> <p>Universal, Industry Standard Threads Flanged for less friction and fastest penetration while drilling</p> <p>Machined (Thick Wall) Barrels To Tightest Specs</p> <p>*Trapezoid Diamond Segments</p>	LR3C	Any SKU / Modelo	
 <p>Core Drill Bits KO</p> <p>Universal, Industry Standard Threads Flanged for less friction and fastest penetration while drilling</p> <p>Machined (Thick Wall) Barrels To Tightest Specs</p> <p>*Trapezoid Diamond Segments</p>	LR2C	Any SKU / Modelo	
 <p>Core Drill Bits KO</p> <p>Universal, Industry Standard Threads Flanged for less friction and fastest penetration while drilling</p> <p>Machined (Thick Wall) Barrels To Tightest Specs</p> <p>*Trapezoid Diamond Segments</p>	LR2.5C	Any SKU / Modelo	
 <p>Core Drill Bits KO</p> <p>Universal, Industry Standard Threads Flanged for less friction and fastest penetration while drilling</p> <p>Machined (Thick Wall) Barrels To Tightest Specs</p> <p>*Trapezoid Diamond Segments</p>	LR2.25C	Any SKU / Modelo	

Imagen	SKU	Descripción	SKU / Modelo
 <p>Core Drill Bits KO</p> <p>Universal, Industry Standard Threads Flanged for less friction and fastest penetration while drilling</p> <p>*Trapezoid Diamond Segments</p> <p>Machined (Thick Wall) Barrels To Tightest Specs</p>	LR1C	Any SKU / Modelo	
 <p>Core Drill Bits KO</p> <p>Universal, Industry Standard Threads Flanged for less friction and fastest penetration while drilling</p> <p>*Trapezoid Diamond Segments</p> <p>Machined (Thick Wall) Barrels To Tightest Specs</p>	LR1.25C	Any SKU / Modelo	
 <p>Core Drill Bits KO</p> <p>Universal, Industry Standard Threads Flanged for less friction and fastest penetration while drilling</p> <p>*Trapezoid Diamond Segments</p> <p>Machined (Thick Wall) Barrels To Tightest Specs</p>	LR1.5C	Any SKU / Modelo	

INFORMACIÓN ADICIONAL

SKU / Modelo

COTECNO