

CÁMARA SEESNAKE NORMAL



SKU: N / A | **Categorías:** [Carretes y cámaras](#), [Desagües y alcantarillado](#), [Diagnóstico](#), [Ensayos no destructivos](#), [Inspección por vídeo de desagüe y alcantarillado](#), [Inspección Y Localización](#) | **Etiquetas:** [Ridgid](#)

DESCRIPCIÓN DEL PRODUCTO

```
[vc_row type="in_container" full_screen_row_position="middle" scene_position="center" text_color="dark" text_align="left" overlay_strength="0.3"][vc_column column_padding="no-extra-padding" column_padding_position="all" background_color_opacity="1" background_hover_color_opacity="1" column_shadow="none" width="1/2" tablet_text_alignment="default" phone_text_alignment="default" column_border_width="none" column_border_style="solid"][tabbed_section style="default" alignment="left"][/tabbed_section] [/vc_column] [vc_column column_padding="no-extra-padding" column_padding_position="all" background_color_opacity="1" background_hover_color_opacity="1" column_shadow="none" width="1/2" tablet_text_alignment="default" phone_text_alignment="default" column_border_width="none" column_border_style="solid"] [vc_row_inner column_margin="default" text_align="left"] [vc_column_inner column_padding="no-extra-padding" column_padding_position="all" background_color_opacity="1" width="1/1" column_border_width="none" column_border_style="solid"] [vc_column_text]
```

Cámara SeeSnake® normal

Los sistemas de inspección de vídeo SeeSnake ofrecen fiabilidad y rendimiento sin igual en un conjunto muy resistente. Cada sistema ofrece:

- Elija entre una cámara SeeSnake normal o las cámaras autonivelantes para obtener imágenes verticales siempre.
- Óptima duración del conjunto de resortes de la cabeza de cámara, totalmente en acero inoxidable templado.
- Resistentes luces de gran intensidad que ofrecen visualización y duración excepcionales.
- Los transmisores flexibles facilitan la localización y son compatibles con los localizadores RIDGID®.
- Pueden utilizarse con cualquier monitor o grabadora SeeSnake.
- Tuberías de 2" a 12" (5 - 30 cm), longitud máxima de 325 pies (99 m).
- La amplia gama de diámetros de tubo hace que este sistema sea ideal para necesidades de inspección muy diversas.

```
[/vc_column_text] [/vc_column_inner] [/vc_row_inner] [/vc_column] [/vc_row] [vc_row type="in_container" full_screen_row_position="middle" scene_position="center" text_color="dark" text_align="left" overlay_strength="0.3"] [vc_column column_padding="no-extra-padding" column_padding_position="all" background_color_opacity="1" background_hover_color_opacity="1" column_shadow="none" width="1/1" tablet_text_alignment="default" phone_text_alignment="default" column_border_width="none" column_border_style="solid"]
```

```
[/vc_column] [/vc_row] [vc_row type="in_container" full_screen_row_position="middle" scene_position="center" text_color="dark" text_align="left" overlay_strength="0.3"] [vc_column column_padding="no-extra-padding" column_padding_position="all" background_color_opacity="1" background_hover_color_opacity="1" column_shadow="none" width="1/1" tablet_text_alignment="default" phone_text_alignment="default" column_border_width="none" column_border_style="solid"] [tabbed_section style="default" alignment="left"] [/tabbed_section] [/vc_column] [/vc_row]
```

INFORMACIÓN ADICIONAL

COTECNO