

CILINDROS DE PRUEBA CALENTADOS



[vc_row][vc_column][vc_table][14px],[14px;align-center;b]Cilindros%20de%20prueba%20calentados[[14px]2472,[14px]Camisa%20calefactora%20con%20cilindro%20de%20prueba%20de%201.125%20%22%2C%20completa%20con%20calentador%20de%20banda%2C%20aislamiento%2C%20termostato%2C%20carcasa%20de%20acero%20inoxidable%2C%20manija%20y%20cable%20el%3%A9ctrico%20de%20350%20vatios.%20Rango%20de%20temperatura%20de%20hasta%20600%20grados%20F.%20Fuerza%20m%C3%A1xima%2035%2C000%20lbs.%2C%20Carga%20aplicada%20a%20400%20grados.%20F.%20Ofrecido%20en%20115%2F230%20voltios%2C%20voltaje%20de%20suministro%20de%201ph%20(por%20favor%20especificue)%20Nota%3A%20No%20debe%20usarse%20con%20prensas%20modelo%204350%2C%20mini%20C%2C%20modelo%20C%20o%20prensas%20calentadas.][14px]2417,[14px]Camisa%20calefactora%20con%20cilindro%20de%20prueba%20de%202.25%20%22%2C%20completa%20con%20calentador%20de%20banda%2C%20aislamiento%2C%20termostato%2C%20carcasa%20de%20acero%20inoxidable%2C%20manija%20y%20cable%20el%3%A9ctrico%20de%20350%20vatios.%20Rango%20de%20temperatura%20de%20hasta%20600%20grados%20F.%20Fuerza%20m%C3%A1xima%2099%2C000%20lbs.%2C%20Carga%20aplicada%20a%20400%20grados.%20F.%20Ofrecido%20en%20115%2F230%20voltios%2C%20voltaje%20de%20suministro%20de%201ph%20(por%20favor%20especificue)%20Nota%3A%20No%20debe%20usarse%20con%20prensas%20modelo%204350%2C%20mini%20C%2C%20modelo%20C%20o%20prensas%20calentadas.[/vc_table][/vc_column][/vc_row]

SKU: N / A | **Categorías:** [ASTM / Moldes especiales](#) |

INFORMACIÓN ADICIONAL

COTECNO