


CONSISTÓMETRO VEBE



SKU: N / A | **Categorías:** [Maquinas de compresión y flexión de Hormigón](#) | **Etiquetas:** [ASTM C1170](#), [ASTM C1176](#), [EN12350-3](#)

VARIACIONES

Imagen	SKU	Descripción	SKU / Modelo
	B-01-03-06-220101	Dimensiones (cm): 26x38x71 Peso (kg): 53 Potencia: 220 V, 60 Hz, 1 ph	B-01-03-06-220101
	B-01-03-06-220201	Dimensiones (cm): 26x38x71 Peso (kg): 53 Potencia: 220 V, 60 Hz, 1 ph	B-01-03-06-220201
	B-01-03-06-220301	Dimensiones (cm): 26x38x71 Peso (kg): 53 Potencia: 220 V, 60 Hz, 1 ph	B-01-03-06-220301
	B-01-03-06-220401	Dimensiones (cm): 26x38x71 Peso (kg): 53 Potencia: 220 V, 60 Hz, 1 ph	B-01-03-06-220401
	B-01-03-06-220501	Dimensiones (cm): 26x38x71 Peso (kg): 53 Potencia: 220 V, 60 Hz, 1 ph	B-01-03-06-220501

Imagen	SKU	Descripción	SKU / Modelo
	B-01-03-06-220601	Dimensiones (cm): 26x38x71 Peso (kg): 53 Potencia: 220 V, 60 Hz, 1 ph	B-01-03-06-220601

COTECNO

DESCRIPCIÓN DEL PRODUCTO

```
[vc_row type="in_container" full_screen_row_position="middle" column_margin="default" scene_position="center"
text_color="dark" text_align="left" overlay_strength="0.3" shape_divider_position="bottom"
bg_image_animation="none"][vc_column column_padding="no-extra-padding" column_padding_position="all"
background_color_opacity="1" background_hover_color_opacity="1" column_link_target="_self" column_shadow="none"
column_border_radius="none" width="1/1" tablet_width_inherit="default" tablet_text_alignment="default"
phone_text_alignment="default" overlay_strength="0.3" column_border_width="none" column_border_style="solid"
bg_image_animation="none"][tabbed_section style="default" alignment="left" spacing="default" tab_color="Accent-
Color"][/tabbed_section][vc_column][vc_row]
```

INFORMACIÓN ADICIONAL

COTECNO