

## DADOS DE PELLETS



[vc\_row][vc\_column][vc\_table][align-center;14px]%23,[align-center;14px;b]Datos%20de%20pellets[[14px]4417,[14px]Troquel%20de%20pellet%20de%206%20mm%2C%20construido%20en%20acero%20inoxidable%20440%2C%20excepto%20eyector.%20Completo%20con%20C3%A9mbolo%2C%20cilindro%2C%20tap%2C%20base%2C%20eyector%20y%20(2)%20yunques.%20Carga%20m%2C%20A1xima%20aplicada%203%2C500%20lbs.][14px]4946,[14px]Troquel%20de%20pellet%20de%2012%20mm%2C%20construido%20en%20acero%20inoxidable%20440%2C%20excepto%20eyector.%20Completo%20con%20C3%A9mbolo%2C%20cilindro%2C%20tap%2C%20base%2C%20eyector%20y%20(2)%20yunques.%20Carga%20m%2C%20A1xima%20aplicada%2013%2C000%20lbs.][14px]3619,[14px]Troquel%20de%20pellet%20de%2013%20mm%2C%20construido%20en%20acero%20inoxidable%20440%2C%20excepto%20eyector.%20Completo%20con%20C3%A9mbolo%2C%20cilindro%2C%20tap%2C%20base%2C%20eyector%20y%20(2)%20yunques.%20Carga%20m%2C%20A1xima%20aplicada%2018%2C000%20lbs.][14px]4369,[14px]Troquel%20de%20pellet%20de%2025%20mm%2C%20construido%20en%20acero%20inoxidable%20440%2C%20excepto%20eyector.%20Completo%20con%20C3%A9mbolo%2C%20cilindro%2C%20tap%2C%20base%2C%20eyector%20y%20(2)%20yunques.%20Carga%20m%2C%20A1xima%20aplicada%2047%2C000%20lbs.][14px]3902,[14px]Troquel%20de%20pellet%20de%2031%20mm%2C%20construido%20en%20acero%20inoxidable%20440%2C%20excepto%20eyector.%20Completo%20con%20C3%A9mbolo%2C%20cilindro%2C%20tap%2C%20base%2C%20eyector%20y%20(2)%20yunques.%20Carga%20m%2C%20A1xima%20aplicada%2060%2C000%20lbs.][14px]3876,[14px]Troquel%20de%20pellet%20de%2040%20mm%2C%20construido%20en%20acero%20inoxidable%20440%2C%20excepto%20eyector.%20Completo%20con%20C3%A9mbolo%2C%20cilindro%2C%20tap%2C%20base%2C%20eyector%20y%20(2)%20yunques.%20Carga%20m%2C%20A1xima%20aplicada%2070%2C000%20lbs.][14px]818744C,[14px]Punz%2C%20B3n%20farmac%2C%20A9utico%20y%20porta%20matrices%20solo%20para%20herramientas%20de%20tipo%20BB2.%20(No%20incluye%20troqueles)][14px]3874,[14px]Bomba%20de%20vac%2C%20ADo%20utilizada%20con%20prensas%20de%20pellets%20para%20evacuar%20troqueles%20de%20pellets.%20Incluye%20medidor%20de%20vac%2C%20ADo%20y%20tuber%2C%20ADa%20de%20conexi%2C%20B3n.%20Disponible%20en%20115V%20o%20230V.%20(Por%20favor%20especifica)][/vc\_table][[/vc\_column][[/vc\_row]

**SKU:** N / A | **Categorías:** [ASTM](#) / [Moldes especiales](#) |

## INFORMACIÓN ADICIONAL

COTECNO