

## DISPOSITIVOS DE LECTURA - MEDIDORES



SKU: N / A | Categorías: [Precipitación](#) |

## DESCRIPCIÓN DEL PRODUCTO

[vc\_row type="in\_container" full\_screen\_row\_position="middle" column\_margin="default" scene\_position="center" text\_color="dark" text\_align="left" overlay\_strength="0.3" shape\_divider\_position="bottom" bg\_image\_animation="none"][vc\_column column\_padding="no-extra-padding" column\_padding\_position="all" background\_color\_opacity="1" background\_hover\_color\_opacity="1" column\_link\_target="\_self" column\_shadow="none" column\_border\_radius="none" width="1/1" tablet\_width\_inherit="default" tablet\_text\_alignment="default" phone\_text\_alignment="default" overlay\_strength="0.3" column\_border\_width="none" column\_border\_style="solid" bg\_image\_animation="none"][vc\_column\_text]**Dispositivos de lectura - medidores**

Los medidores de precipitación analógicos con dispositivo de medición y lectura incluido sirven para la determinación manual exacta de la precipitación.[vc\_column\_text][vc\_row\_inner column\_margin="default" text\_align="left" css=".vc\_custom\_1597668708409{border-radius: 2px !important;}"][vc\_column\_inner column\_padding="no-extra-padding" column\_padding\_position="all" background\_color="#9492ff" background\_color\_opacity="1" background\_hover\_color\_opacity="1" font\_color="ffffff" column\_shadow="none" column\_border\_radius="none" column\_link\_target="\_self" width="1/4" tablet\_width\_inherit="default" overlay\_strength="0.3" column\_border\_width="none" column\_border\_style="solid" bg\_image\_animation="none"][vc\_column\_text]

### Imagen

[vc\_column\_text][vc\_column\_inner][vc\_column\_inner column\_padding="no-extra-padding" column\_padding\_position="all" background\_color="#9492ff" background\_color\_opacity="1" background\_hover\_color\_opacity="1" font\_color="ffffff" column\_shadow="none" column\_border\_radius="none" column\_link\_target="\_self" width="1/4" tablet\_width\_inherit="default" overlay\_strength="0.3" column\_border\_width="none" column\_border\_style="solid" bg\_image\_animation="none"][vc\_column\_text]

### Nombre del Producto

[vc\_column\_text][vc\_column\_inner][vc\_column\_inner column\_padding="no-extra-padding" column\_padding\_position="all" background\_color="#9492ff" background\_color\_opacity="1" background\_hover\_color\_opacity="1" font\_color="ffffff" column\_shadow="none" column\_border\_radius="none" column\_link\_target="\_self" width="1/2" tablet\_width\_inherit="default" overlay\_strength="0.3" column\_border\_width="none" column\_border\_style="solid" bg\_image\_animation="none"][vc\_column\_text]

### Descripción corta

[vc\_column\_text][vc\_column\_inner][vc\_row\_inner][vc\_row\_inner column\_margin="default" text\_align="left"][vc\_column\_inner column\_padding="no-extra-padding" column\_padding\_position="all" background\_color\_opacity="1" background\_hover\_color\_opacity="1" column\_shadow="none" column\_border\_radius="none" column\_link\_target="\_self" width="1/4" tablet\_width\_inherit="default" overlay\_strength="0.3" column\_border\_width="none" column\_border\_style="solid" bg\_image\_animation="none"][image\_with\_animation image\_url="138409" alignment="center" animation="Fade In" hover\_animation="none" border\_radius="none" box\_shadow="none" image\_loading="default" max\_width="100%" max\_width\_mobile="default"][vc\_column\_inner][vc\_column\_inner column\_padding="no-extra-padding" column\_padding\_position="all" background\_color\_opacity="1" background\_hover\_color\_opacity="1" column\_shadow="none" column\_border\_radius="none" column\_link\_target="\_self" width="1/4" tablet\_width\_inherit="default" overlay\_strength="0.3" column\_border\_width="none" column\_border\_style="solid" bg\_image\_animation="none"][vc\_column\_text]

Medidor De Precipitaciones Acc. A Hellmann

5.4000.00.000[vc\_column\_text][vc\_column\_inner][vc\_column\_inner column\_padding="no-extra-padding"

```
column_padding_position="all" background_color_opacity="1" background_hover_color_opacity="1"
column_shadow="none" column_border_radius="none" column_link_target="_self" width="1/2"
tablet_width_inherit="default" overlay_strength="0.3" column_border_width="none" column_border_style="solid"
bg_image_animation="none"]vc_column_text]La precipitación se recoge en un recipiente y luego se mide en litros en la
probeta.[vc_column_text][nectar_cta btn_style="see-through" heading_tag="h6" button_color="default"
link_type="new_tab" alignment="left" display="block" link_text="Leer más"
url="http://test.cotecno.cl/nuestros-productos/medidor-de-precipitaciones/"]vc_column_inner][vc_row_inner]
```

```
[vc_row_inner column_margin="default" text_align="left"]vc_column_inner column_padding="no-extra-padding"
column_padding_position="all" background_color_opacity="1" background_hover_color_opacity="1"
column_shadow="none" column_border_radius="none" column_link_target="_self" width="1/4"
tablet_width_inherit="default" overlay_strength="0.3" column_border_width="none" column_border_style="solid"
bg_image_animation="none"]image_with_animation image_url="138410" alignment="center" animation="Fade In"
hover_animation="none" border_radius="none" box_shadow="none" image_loading="default" max_width="100%"
max_width_mobile="default"]vc_column_inner][vc_column_inner column_padding="no-extra-padding"
column_padding_position="all" background_color_opacity="1" background_hover_color_opacity="1"
column_shadow="none" column_border_radius="none" column_link_target="_self" width="1/4"
tablet_width_inherit="default" overlay_strength="0.3" column_border_width="none" column_border_style="solid"
bg_image_animation="none"]vc_column_text]
```

Medidor De Lluvia Y Nieve Acc. A Hellmann

```
5.4001.00.000]vc_column_text][vc_column_inner][vc_column_inner column_padding="no-extra-padding"
column_padding_position="all" background_color_opacity="1" background_hover_color_opacity="1"
column_shadow="none" column_border_radius="none" column_link_target="_self" width="1/2"
tablet_width_inherit="default" overlay_strength="0.3" column_border_width="none" column_border_style="solid"
bg_image_animation="none"]vc_column_text]La precipitación se recoge en un recipiente y luego se mide en litros en la
probeta.[vc_column_text][nectar_cta btn_style="see-through" heading_tag="h6" button_color="default"
link_type="new_tab" alignment="left" display="block" link_text="Leer más"
url="http://test.cotecno.cl/nuestros-productos/medidor-de-lluvia/"]vc_column_inner][vc_row_inner]
```

```
[vc_column][vc_row]
```

## INFORMACIÓN ADICIONAL

COTECNO