

DISPOSITIVOS DE MEDICIÓN MÓVILES



SKU: N / A | **Categorías:** [Dispositivos varios](#) |

DESCRIPCIÓN DEL PRODUCTO

```
[vc_row type="in_container" full_screen_row_position="middle" column_margin="default" scene_position="center"
text_color="dark" text_align="left" overlay_strength="0.3" shape_divider_position="bottom"
bg_image_animation="none"][vc_column column_padding="no-extra-padding" column_padding_position="all"
background_color_opacity="1" background_hover_color_opacity="1" column_link_target="_self" column_shadow="none"
column_border_radius="none" width="1/1" tablet_width_inherit="default" tablet_text_alignment="default"
phone_text_alignment="default" overlay_strength="0.3" column_border_width="none" column_border_style="solid"
bg_image_animation="none"][vc_row_inner column_margin="default" text_align="left"
css=".vc_custom_1597668708409{border-radius: 2px !important;}"[vc_column_inner column_padding="no-extra-padding"
column_padding_position="all" background_color="#9492ff" background_color_opacity="1"
background_hover_color_opacity="1" font_color="#ffffff" column_shadow="none" column_border_radius="none"
column_link_target="_self" width="1/4" tablet_width_inherit="default" overlay_strength="0.3"
column_border_width="none" column_border_style="solid" bg_image_animation="none"][vc_column_text]
```

Imagen

```
[/vc_column_text][vc_column_inner][vc_column_inner column_padding="no-extra-padding" column_padding_position="all"
background_color="#9492ff" background_color_opacity="1" background_hover_color_opacity="1" font_color="#ffffff"
column_shadow="none" column_border_radius="none" column_link_target="_self" width="1/4"
tablet_width_inherit="default" overlay_strength="0.3" column_border_width="none" column_border_style="solid"
bg_image_animation="none"][vc_column_text]
```

Nombre del Producto

```
[/vc_column_text][vc_column_inner][vc_column_inner column_padding="no-extra-padding" column_padding_position="all"
background_color="#9492ff" background_color_opacity="1" background_hover_color_opacity="1" font_color="#ffffff"
column_shadow="none" column_border_radius="none" column_link_target="_self" width="1/2"
tablet_width_inherit="default" overlay_strength="0.3" column_border_width="none" column_border_style="solid"
bg_image_animation="none"][vc_column_text]
```

Descripción corta

```
[/vc_column_text][vc_column_inner][vc_row_inner][vc_row_inner column_margin="default"
text_align="left"][vc_column_inner column_padding="no-extra-padding" column_padding_position="all"
background_color_opacity="1" background_hover_color_opacity="1" column_shadow="none"
column_border_radius="none" column_link_target="_self" width="1/4" tablet_width_inherit="default"
overlay_strength="0.3" column_border_width="none" column_border_style="solid"
bg_image_animation="none"][image_with_animation image_url="138350" alignment="center" animation="Fade In"
hover_animation="none" border_radius="none" box_shadow="none" image_loading="default" max_width="100%"
max_width_mobile="default"][/vc_column_inner][vc_column_inner column_padding="no-extra-padding"
column_padding_position="all" background_color_opacity="1" background_hover_color_opacity="1"
column_shadow="none" column_border_radius="none" column_link_target="_self" width="1/4"
tablet_width_inherit="default" overlay_strength="0.3" column_border_width="none" column_border_style="solid"
bg_image_animation="none"][vc_column_text]
```

Handylog

```
4.3406.10.000[/vc_column_text][vc_column_inner][vc_column_inner column_padding="no-extra-padding"
column_padding_position="all" background_color_opacity="1" background_hover_color_opacity="1"
```

column_shadow="none" column_border_radius="none" column_link_target="_self" width="1/2"
tablet_width_inherit="default" overlay_strength="0.3" column_border_width="none" column_border_style="solid"
bg_image_animation="none"]
[vc_column_text]El "Anemómetro digital" sirve para medir y registrar la velocidad del viento y es adecuado para uso móvil.
[vc_column_text]
[nectar_cta btn_style="see-through" heading_tag="h6"
button_color="default" link_type="new_tab" alignment="left" display="block" link_text="Leer más"
url="http://test.cotecno.cl/nuestros-productos/handylog/"]
[/vc_column_inner]
[/vc_row_inner]

[/vc_column]
[/vc_row]

COTECNO

INFORMACIÓN ADICIONAL

COTECNO