

## EATON LOFMEM G LMG-30-0.2-4S FILTER CARTRIDGE



**SKU:** LMG-30-0.2-4S DuP | **Categorías:** [Equipo Analítico](#) | **Etiquetas:** [brand|Lenntech](#)

## DESCRIPCIÓN DEL PRODUCTO

### EATON LOFMEM G LMG-30-0.2-4S FILTER CARTRIDGE

**PART NUMBER: LMG-30-0.2-4S**

[Please contact us for more information and/or a quotation request.](#)

#### Specifications

Brand	Eaton LOFMEM G
Model	LMG 30 0.2 4S
Pore Size $\mu$	0.2

#### Dimensions / Weights

Length in inch	30.0
Length in cm	76.2
Quantity per case	12 pieces



[Download Datasheet](#)

[BUY NOW](#)

[Request for Quote](#)



## LOFMEM G SERIES CARTRIDGE FILTERS

The LOFMEM-G pleated, disposable membrane filter cartridges are one of the industry's most efficient and cost effective filters available.

#### Features / Benefits

- Large membrane surface area for high throughput
- Longer on-line service reduces costly maintenance time
- Absolute rated membrane from 0.1 to 0.65  $\mu\text{m}$
- Manufactured in an ISO Class 7 cleanroom environment
- 100% flushed with 18 M $\Omega$ -cm DI water and bubblepoint tested
- Meets USP Class VI biological test for plastics
- Fixed pore construction eliminates dirt unloading as differential pressure increases
- Low extractables

### Filter Specifications

- **Media**

Asymmetric polyethersulfone membrane

- **Inner core, end caps, cage**

Polypropylene

- **Support layers**

Spunbond polypropylene

- **Gaskets/O-Rings**

Buna-N, EPDM, Silicone, Viton<sup>®</sup>, FEP encapsulated Viton O-Rings

- **Micron ratings**

0.1; 0.2; 0.45; 0.65  $\mu\text{m}$

### Typical Applications

LOFMEM-G cartridges from Eaton are inherently hydrophilic and are designed for a wide range of applications, including food & beverage, filtration of acids & bases, cosmetics, inks, chemicals, ultra-pure water and other aqueous solutions.

## INFORMACIÓN ADICIONAL

<b>url_fab</b>	<a href="https://www.lenntech.com/products/Eaton-LOFMEM-G/LMG-30-0.2-4S/LMG-30-0.2-4S-Filter-Cartridge/index.html">https://www.lenntech.com/products/Eaton-LOFMEM-G/LMG-30-0.2-4S/LMG-30-0.2-4S-Filter-Cartridge/index.html</a>
<b>brand</b>	Lenntech

COTECNO