

## EATON LOFMEM T LMT-10-0.05-DOES FILTER CARTRIDGE



**SKU:** LMT-10-0.05-DOES DuP | **Categorías:** [Equipo Analítico](#) | **Etiquetas:** [brand|Lenntech](#)

COTECNO

## DESCRIPCIÓN DEL PRODUCTO

### EATON LOFMEM T LMT-10-0.05-DOES FILTER CARTRIDGE

**PART NUMBER: LMT-10-0.05-DOES**

[Please contact us for more information and/or a quotation request.](#)

#### Specifications

|                 |                  |
|-----------------|------------------|
| Brand           | Eaton LOFMEM T   |
| Model           | LMT 10 0.05 DOES |
| Pore Size $\mu$ | 0.05             |

#### Dimensions / Weights

|                   |           |
|-------------------|-----------|
| Length in inch    | 10.0      |
| Length in cm      | 25.4      |
| Quantity per case | 12 pieces |



[Download Datasheet](#)

[BUY NOW](#)

[Request for Quote](#)



## LOFMEM T SERIES CARTRIDGE FILTERS

The LOFMEM-T membrane filter cartridges are ideal for applications such as strong acids/bases, compressed gases, photoresists and hot DI water.

#### Features / Benefits

- High flow rates and high surface area minimise total system size requirements
- Full traceability marking
- Integrity testing and 100% flushing with 18 M $\Omega$ -cm de-ionized water prior to shipment
- Validated to USP Class VI biological Standards for Plastics
- Manufactured in ISO Class 7 Cleanroom Environment

### **Filter Specifications**

- **Media**

Gore-Tex® expanded PTFE membrane

- **Inner core, end caps, cage**

Polypropylene

- **Support layers**

polypropylene

- **O-Rings**

Buna-N, EPDM, Silicone, Viton©, FEP encapsulated Viton

- **Micron ratings**

0.05; 0.1; 0.2; 0.45; 1.0  $\mu$ m

### **Typical Applications**

LOFTMEM-T cartridges from Eaton are ideal for gas/vent applications and the filtration of aggressive compounds.< br/> Specific uses include: strong acids/bases, compressed gases, photoresists, pharmaceutical intermediates, hot DI water and fermentation air.

## INFORMACIÓN ADICIONAL

**url\_fab** <https://www.lenntech.com/products/Eaton-LOFMEM-T/LMT-10-0.05-DOES/LMT-10-0.05-DOES-Filter-Cartridge/index.html>

**brand** Lenntech

COTECNO