

EATON LOFMEM T LMT-10-0.1-4S FILTER CARTRIDGE



SKU: LMT-10-0.1-4S DuP | **Categorías:** [Equipo Analítico](#) | **Etiquetas:** [brand|Lenntech](#)

COTECNO

DESCRIPCIÓN DEL PRODUCTO

EATON LOFMEM T LMT-10-0.1-4S FILTER CARTRIDGE

PART NUMBER: LMT-10-0.1-4S

[Please contact us for more information and/or a quotation request.](#)

Specifications

Brand	Eaton LOFMEM T
Model	LMT 10 0.1 4S
Pore Size μ	0.1

Dimensions / Weights

Length in inch	10.0
Length in cm	25.4
Quantity per case	12 pieces



[Download Datasheet](#)

[BUY NOW](#)

[Request for Quote](#)



LOFMEM T SERIES CARTRIDGE FILTERS

The LOFMEM-T membrane filter cartridges are ideal for applications such as strong acids/bases, compressed gases, photoresists and hot DI water.

Features / Benefits

- High flow rates and high surface area minimise total system size requirements
- Full traceability marking
- Integrity testing and 100% flushing with 18 M Ω -cm de-ionized water prior to shipment
- Validated to USP Class VI biological Standards for Plastics
- Manufactured in ISO Class 7 Cleanroom Environment

Filter Specifications

- **Media**

Gore-Tex® expanded PTFE membrane

- **Inner core, end caps, cage**

Polypropylene

- **Support layers**

polypropylene

- **O-Rings**

Buna-N, EPDM, Silicone, Viton©, FEP encapsulated Viton

- **Micron ratings**

0.05; 0.1; 0.2; 0.45; 1.0 μ m

Typical Applications

LOFTMEM-T cartridges from Eaton are ideal for gas/vent applications and the filtration of aggressive compounds.< br/> Specific uses include: strong acids/bases, compressed gases, photoresists, pharmaceutical intermediates, hot DI water and fermentation air.

INFORMACIÓN ADICIONAL

url_fab <https://www.lenntech.com/products/Eaton-LOFMEM-T/LMT-10-0.1-4S/LMT-10-0.1-4S-Filter-Cartridge/index.html>

brand Lenntech

COTECNO