

## EATON LOFMEM T LMT-10-1.0-2S FILTER CARTRIDGE



**SKU:** LMT-10-1.0-2S DuP | **Categorías:** [Equipo Analítico](#) | **Etiquetas:** [brand|Lenntech](#)

## DESCRIPCIÓN DEL PRODUCTO

### EATON LOFMEM T LMT-10-1.0-2S FILTER CARTRIDGE

**PART NUMBER: LMT-10-1.0-2S**

[Please contact us for more information and/or a quotation request.](#)

#### Specifications

Brand	Eaton LOFMEM T
Model	LMT 10 1.0 2S
Pore Size $\mu$	1.0

#### Dimensions / Weights

Length in inch	10.0
Length in cm	25.4
Quantity per case	12 pieces



[Download Datasheet](#)

[BUY NOW](#)

[Request for Quote](#)



## LOFMEM T SERIES CARTRIDGE FILTERS

The LOFMEM-T membrane filter cartridges are ideal for applications such as strong acids/bases, compressed gases, photoresists and hot DI water.

#### Features / Benefits

- High flow rates and high surface area minimise total system size requirements
- Full traceability marking
- Integrity testing and 100% flushing with 18 M $\Omega$ -cm de-ionized water prior to shipment
- Validated to USP Class VI biological Standards for Plastics
- Manufactured in ISO Class 7 Cleanroom Environment

### **Filter Specifications**

- **Media**

Gore-Tex® expanded PTFE membrane

- **Inner core, end caps, cage**

Polypropylene

- **Support layers**

polypropylene

- **O-Rings**

Buna-N, EPDM, Silicone, Viton©, FEP encapsulated Viton

- **Micron ratings**

0.05; 0.1; 0.2; 0.45; 1.0  $\mu$ m

### **Typical Applications**

LOFTMEM-T cartridges from Eaton are ideal for gas/vent applications and the filtration of aggressive compounds. < br/> Specific uses include: strong acids/bases, compressed gases, photoresists, pharmaceutical intermediates, hot DI water and fermentation air.

## INFORMACIÓN ADICIONAL

<b>url_fab</b>	<a href="https://www.lenntech.com/products/Eaton-LOFMEM-T/LMT-10-1.0-2S/LMT-10-1.0-2S-Filter-Cartridge/index.html">https://www.lenntech.com/products/Eaton-LOFMEM-T/LMT-10-1.0-2S/LMT-10-1.0-2S-Filter-Cartridge/index.html</a>
<b>brand</b>	Lenntech

COTECNO