

## EATON LOFMEM T LMT-5-0.1-DOES FILTER CARTRIDGE



**SKU:** LMT-5-0.1-DOES DuP | **Categorías:** [Equipo Analítico](#) | **Etiquetas:** [brand|Lenntech](#)

## DESCRIPCIÓN DEL PRODUCTO

### EATON LOFMEM T LMT-5-0.1-DOES FILTER CARTRIDGE

**PART NUMBER: LMT-5-0.1-DOES**

[Please contact us for more information and/or a quotation request.](#)

#### Specifications

Brand	Eaton LOFMEM T
Model	LMT 5 0.1 DOES
Pore Size $\mu$	0.1

#### Dimensions / Weights

Length in inch	5.0
Length in cm	12.7
Quantity per case	12 pieces



[Download Datasheet](#)



## LOFMEM T SERIES CARTRIDGE FILTERS

The LOFMEM-T membrane filter cartridges are ideal for applications such as strong acids/bases, compressed gases, photoresists and hot DI water.

#### Features / Benefits

- High flow rates and high surface area minimise total system size requirements
- Full traceability marking

- Integrity testing and 100% flushing with 18 M $\Omega$ -cm de-ionized water prior to shipment
- Validated to USP Class VI biological Standards for Plastics
- Manufactured in ISO Class 7 Cleanroom Environment

#### **Filter Specifications**

- **Media**

Gore-Tex® expanded PTFE membrane

- **Inner core, end caps, cage**

Polypropylene

- **Support layers**

polypropylene

- **O-Rings**

Buna-N, EPDM, Silicone, Viton©, FEP encapsulated Viton

- **Micron ratings**

0.05; 0.1; 0.2; 0.45; 1.0  $\mu$ m

#### **Typical Applications**

LOFTMEM-T cartridges from Eaton are ideal for gas/vent applications and the filtration of aggressive compounds. < br/> Specific uses include: strong acids/bases, compressed gases, photoresists, pharmaceutical intermediates, hot DI water and fermentation air.

## INFORMACIÓN ADICIONAL

**url\_fab** <https://www.lenntech.com/products/Eaton-LOFMEM-T/LMT-5-0.1-DOES/LMT-5-0.1-DOES-Filter-Cartridge/index.html>

**brand** Lenntech

COTECNO