

EATON LOFMEM W LMW-40-0.65-DOES FILTER CARTRIDGE



SKU: LMW-40-0.65-DOES DuP | **Categorías:** [Equipo Analítico](#) | **Etiquetas:** [brand|Lenntech](#)

COTECNO

DESCRIPCIÓN DEL PRODUCTO

EATON LOFMEM W LMW-40-0.65-DOES FILTER CARTRIDGE

PART NUMBER: LMW-40-0.65-DOES

[Please contact us for more information and/or a quotation request.](#)

Specifications

Brand	Eaton LOFMEM W
Model	LMW 40 0.65 DOES
Pore Size μ	0.65

Dimensions / Weights

Length in inch	40.0
Length in cm	101.6
Quantity per case	12 pieces



[Download Datasheet](#)



LOFMEM W SERIES CARTRIDGE FILTERS

This disposable Eaton membrane filter cartridge is designed using absolute rated polypropylene and polyethersulfone components that are both hydrophilic and asymmetric.

Engineered specifically for economic overall filtration, the LOFMEM-W offers superior flow rates and throughputs.

Features / Benefits

- High dirt holding provides long service life and reduced maintenance requirements

- Economic absolute filtration
- FDA listed (U.S. CFR, Title 21) materials of construction for food and beverage contact
- All-thermal bonded construction, no adhesives
- Non-fiber releasing
- No wetting agents
- Validated for USP, Class VI standards for plastics
- Available in multiple configurations

Filter Specifications

- **Media**

Asymmetric polyethersulfone

- **Inner core, end caps, cage**

Polypropylene

- **Support layers**

Spunbond polypropylene

- **Gaskets/O-Rings**

Buna-N, EPDM, Silicone, Viton®, FEP encapsulated Viton (O-Rings only)

- **Micron ratings**

0.05; 0.1; 0.2; 0.45; 0.65 µm

- **Compatibility**

Compatible with most common chemical cleaning, sanitising and sterilising agents and with pH range from 1 to 4. For more information, call Eaton or your Eaton representative

Typical Applications

Eaton's LOFMEM-W membrane filter cartridge is the preferred choice for general water filtration, as a DI water prefilter/postfilter and for use in aqueous-based chemical processing.

INFORMACIÓN ADICIONAL

url_fab <https://www.lenntech.com/products/Eaton-LOFMEM-W/LMW-40-0.65-DOES/LMW-40-0.65-DOES-Filter-Cartridge/index.html>

brand Lenntech

COTECNO