

FILTRACIÓN LENN



SKU: N / A | **Categorías:** [Filtración Lenn](#), [Filtros de sedimentos](#), [Lenntech](#) |

GALERÍA DE IMÁGENES



DESCRIPCIÓN DEL PRODUCTO

[vc_row type="in_container" full_screen_row_position="middle" column_margin="default" scene_position="center" text_color="dark" text_align="left" overlay_strength="0.3" shape_divider_position="bottom" bg_image_animation="none"][vc_column column_padding="no-extra-padding" column_padding_position="all" background_color_opacity="1" background_hover_color_opacity="1" column_link_target="_self" column_shadow="none" column_border_radius="none" width="1/1" tablet_width_inherit="default" tablet_text_alignment="default" phone_text_alignment="default" overlay_strength="0.3" column_border_width="none" column_border_style="solid" bg_image_animation="none"][tabbed_section style="default" alignment="left" spacing="default" tab_color="Accent-Color"][/tabbed_section][vc_row_inner column_margin="default" text_align="left"][vc_column_inner column_padding="no-extra-padding" column_padding_position="all" background_color_opacity="1" background_hover_color_opacity="1" column_shadow="none" column_border_radius="none" column_link_target="_self" width="1/3" tablet_width_inherit="default" overlay_strength="0.3" column_border_width="none" column_border_style="solid" bg_image_animation="none"][vc_column_text]

Cartuchos de PP meltblown

[Lenn CF25101](#) 10 pulgadas

[Lenn CF25105](#) 10 pulgadas

[Lenn CF25110](#) 10 pulgadas

[Lenn CF45105](#) 10 pulgadas

[Lenn CF45202](#) 20 pulgadas

[Lenn CF45205](#) 20 pulgadas

[/vc_column_text][/vc_column_inner][vc_column_inner column_padding="no-extra-padding" column_padding_position="all" background_color_opacity="1" background_hover_color_opacity="1" column_shadow="none" column_border_radius="none" column_link_target="_self" width="1/3" tablet_width_inherit="default" overlay_strength="0.3" column_border_width="none" column_border_style="solid" bg_image_animation="none"][vc_column_text]

Cartuchos de cuerda enrollada

[Lenn KP1](#) 10, 20 pulgadas

[Lenn KP5](#) 10, 20 pulgadas

[Lenn KP10](#) 10, 20 pulgadas

[Lenn KP20](#) 10, 20 pulgadas

[Lenn BB202](#) 20 pulgadas

```
[/vc_column_text][/vc_column_inner][vc_column_inner column_padding="no-extra-padding" column_padding_position="all"
background_color_opacity="1" background_hover_color_opacity="1" column_shadow="none"
column_border_radius="none" column_link_target="_self" width="1/3" tablet_width_inherit="default"
overlay_strength="0.3" column_border_width="none" column_border_style="solid"
bg_image_animation="none"][image_with_animation image_url="158608" alignment="center" animation="Fade In"
hover_animation="none" border_radius="none" box_shadow="none" image_loading="default" max_width="100%"
max_width_mobile="default"][/vc_column_inner][/vc_row_inner]
```

[vc_column_text]

Cartuchos de filtro de carbón

```
[/vc_column_text][vc_row_inner column_margin="default" text_align="left"][vc_column_inner column_padding="no-extra-
padding" column_padding_position="all" background_color_opacity="1" background_hover_color_opacity="1"
column_shadow="none" column_border_radius="none" column_link_target="_self" width="1/2"
tablet_width_inherit="default" overlay_strength="0.3" column_border_width="none" column_border_style="solid"
bg_image_animation="none"]
```

Estos cartuchos eliminan sulfuro de hidrógeno, hierro, cloro, cloramina, ciertos pesticidas, productos derivados del petróleo y partículas de sedimentos.

Material del filtro: Centaur (Calgon Carbon). Es un carbón activado granular bituminoso de alta calidad con propiedades catalíticas

```
[/vc_column_text][/vc_column_inner][vc_column_inner column_padding="no-extra-padding"
column_padding_position="all" background_color_opacity="1" background_hover_color_opacity="1"
column_shadow="none" column_border_radius="none" column_link_target="_self" width="1/2"
tablet_width_inherit="default" overlay_strength="0.3" column_border_width="none" column_border_style="solid"
bg_image_animation="none"]
```

Estos cartuchos eliminan cloro, organoclorados, pesticidas, productos derivados del petróleo y partículas de sedimento.

Material del filtro: carbón activado granular (carbón de cáscara de coco) con componente antibacteriano argéntífero.

```
[/vc_column_text][/vc_column_inner][/vc_row_inner]
```

```
[vc_row_inner column_margin="default" text_align="left"][vc_column_inner column_padding="no-extra-padding"
column_padding_position="all" background_color_opacity="1" background_hover_color_opacity="1"
column_shadow="none" column_border_radius="none" column_link_target="_self" width="1/3"
tablet_width_inherit="default" overlay_strength="0.3" column_border_width="none" column_border_style="solid"
bg_image_animation="none"]
```

Cartuchos de carbono Calgon

[Lenn CENT4510](#) 10 pulgadas

[Lenn CENT4520](#) 20 pulgadas

```
[/vc_column_text][/vc_column_inner][vc_column_inner column_padding="no-extra-padding" column_padding_position="all"
background_color_opacity="1" background_hover_color_opacity="1" column_shadow="none"
column_border_radius="none" column_link_target="_self" width="1/3" tablet_width_inherit="default"
```

overlay_strength="0.3" column_border_width="none" column_border_style="solid"
bg_image_animation="none"]][vc_column_text]

Cartuchos de carbón activado

[Lenn KUD2510](#) 10 pulgadas

[Lenn CHV2510](#) 10 pulgadas

[Lenn KUD4510](#) 10 pulgadas

[Lenn KUD4520](#) 20 pulgadas

[Lenn KUS2510](#) 10 pulgadas

[Lenn KUS4510](#) 10 pulgadas

[Lenn KUS4520](#) 20 pulgadas

[/vc_column_text][vc_column_inner][vc_column_inner column_padding="no-extra-padding" column_padding_position="all"
background_color_opacity="1" background_hover_color_opacity="1" column_shadow="none"
column_border_radius="none" column_link_target="_self" width="1/3" tablet_width_inherit="default"
overlay_strength="0.3" column_border_width="none" column_border_style="solid"
bg_image_animation="none"]][image_with_animation image_url="158618" alignment="center" animation="Fade In"
hover_animation="none" border_radius="none" box_shadow="none" image_loading="default" max_width="100%"
max_width_mobile="default"]][vc_column_inner][vc_row_inner]

[vc_column_text]

Cartuchos LennDepth

[/vc_column_text][vc_column_text]**Documentos PDF**

- [LennDepth ABS \(PDF\)](#)
- [LennHFP \(PDF\)](#)
- [LennHFP Retro \(PDF\)](#)

Detalles de productos

- [Filtros LennBag](#)
- [Filtración Lenn](#)
- [LennDepth](#)

[/vc_column_text][/vc_column][/vc_row]

INFORMACIÓN ADICIONAL

COTECNO