

FILTRO DE CARTUCHO DE REPUESTO



SKU: N / A | **Categorías:** [Filtración Eaton](#) |

DESCRIPCIÓN DEL PRODUCTO

[vc_row type="in_container" full_screen_row_position="middle" column_margin="default" scene_position="center" text_color="dark" text_align="left" overlay_strength="0.3" shape_divider_position="bottom" bg_image_animation="none"][vc_column column_padding="no-extra-padding" column_padding_position="all" background_color_opacity="1" background_hover_color_opacity="1" column_link_target="_self" column_shadow="none" column_border_radius="none" width="1/1" tablet_width_inherit="default" tablet_text_alignment="default" phone_text_alignment="default" overlay_strength="0.3" column_border_width="none" column_border_style="solid" bg_image_animation="none"][tabbed_section style="default" alignment="left" spacing="default" tab_color="Accent-Color"]/[tabbed_section][vc_row_inner column_margin="default" text_align="left"][vc_column_inner column_padding="no-extra-padding" column_padding_position="all" background_color_opacity="1" background_hover_color_opacity="1" column_shadow="none" column_border_radius="none" column_link_target="_self" width="1/2" tablet_width_inherit="default" overlay_strength="0.3" column_border_width="none" column_border_style="solid" bg_image_animation="none"][vc_column_text]

	Longitud	del	cartucho
	5 "(12,7 cm)		
	7 "(17,8 cm)		
	10 "(25,4 cm)		
	20 "(50,8 cm)		
	30 "(76,2 cm)		
	40 "(101,6 cm)		

[vc_column_text][vc_column_inner][vc_column_inner column_padding="no-extra-padding" column_padding_position="all" background_color_opacity="1" background_hover_color_opacity="1" column_shadow="none" column_border_radius="none" column_link_target="_self" width="1/2" tablet_width_inherit="default" overlay_strength="0.3" column_border_width="none" column_border_style="solid" bg_image_animation="none"][image_with_animation image_url="159686" alignment="center" animation="Fade In" hover_animation="none" border_radius="none" box_shadow="none" image_loading="default" max_width="100%" max_width_mobile="default"]/[vc_column_inner][vc_row_inner][vc_column_text]- Micragem: 0.5-1-5-10-25-50-75-100-150 ... micrones

Tipo: hilo herido, Melt-Blown, carbón activado, acero inoxidable, con plisado ...

Aquí está la lista de filtros de cartucho que podemos ofrecer:

[vc_column_text][vc_row_inner column_margin="default" text_align="left"][vc_column_inner column_padding="no-extra-padding" column_padding_position="all" background_color_opacity="1" background_hover_color_opacity="1" column_shadow="none" column_border_radius="none" column_link_target="_self" width="1/4" tablet_width_inherit="default" overlay_strength="0.3" column_border_width="none" column_border_style="solid" bg_image_animation="none"][image_with_animation image_url="158844" alignment="center" animation="Fade In" hover_animation="none" border_radius="none" box_shadow="none" image_loading="default" max_width="100%" max_width_mobile="default"]/[vc_column_inner][vc_column_inner column_padding="no-extra-padding" column_padding_position="all" background_color_opacity="1" background_hover_color_opacity="1" column_shadow="none" column_border_radius="none" column_link_target="_self" width="1/4" tablet_width_inherit="default" overlay_strength="0.3" column_border_width="none" column_border_style="solid" bg_image_animation="none"][image_with_animation image_url="158845" alignment="center" animation="Fade In" hover_animation="none" border_radius="none" box_shadow="none" image_loading="default" max_width="100%" max_width_mobile="default"]/[vc_column_inner][vc_column_inner column_padding="no-extra-padding"

column_padding_position="all" background_color_opacity="1" background_hover_color_opacity="1"
column_shadow="none" column_border_radius="none" column_link_target="_self" width="1/4"
tablet_width_inherit="default" overlay_strength="0.3" column_border_width="none" column_border_style="solid"
bg_image_animation="none"][image_with_animation image_url="158850" alignment="center" animation="Fade In"
hover_animation="none" border_radius="none" box_shadow="none" image_loading="default" max_width="100%"
max_width_mobile="default"][/vc_column_inner][vc_column_inner column_padding="no-extra-padding"
column_padding_position="all" background_color_opacity="1" background_hover_color_opacity="1"
column_shadow="none" column_border_radius="none" column_link_target="_self" width="1/4"
tablet_width_inherit="default" overlay_strength="0.3" column_border_width="none" column_border_style="solid"
bg_image_animation="none"][image_with_animation image_url="158846" alignment="center" animation="Fade In"
hover_animation="none" border_radius="none" box_shadow="none" image_loading="default" max_width="100%"
max_width_mobile="default"][/vc_column_inner][vc_row_inner][vc_column_text]

Cartuchos De Filtro Atlas

Referencia típica : FA-SX-10-25

Tipo: cuerda herida Conexión: sello plano Longitud: 10 "Micragem: 25 micrones

Carcasas Y Filtros De Cartucho Harmsco

[/vc_column_text][vc_row_inner column_margin="default" text_align="left"][vc_column_inner column_padding="no-extra-padding" column_padding_position="all" background_color_opacity="1" background_hover_color_opacity="1"
column_shadow="none" column_border_radius="none" column_link_target="_self" width="1/2"
tablet_width_inherit="default" overlay_strength="0.3" column_border_width="none" column_border_style="solid"
bg_image_animation="none"][/vc_column_text]

Referencia típica : HC / 40-5

[/vc_column_text][vc_column_inner][vc_column_inner column_padding="no-extra-padding" column_padding_position="all" background_color_opacity="1" background_hover_color_opacity="1" column_shadow="none"
column_border_radius="none" column_link_target="_self" width="1/2" tablet_width_inherit="default"
overlay_strength="0.3" column_border_width="none" column_border_style="solid"
bg_image_animation="none"][image_with_animation image_url="159005" alignment="center" animation="Fade In"
hover_animation="none" border_radius="none" box_shadow="none" image_loading="default" max_width="100%"
max_width_mobile="default"][/vc_column_inner][vc_row_inner][vc_column_text]Longitud: 9-5 / 8 "Micragem: 5 mcr

- Cartuchos Hayward

[/vc_column_text][vc_row_inner column_margin="default" text_align="left"][vc_column_inner column_padding="no-extra-padding" column_padding_position="all" background_color_opacity="1" background_hover_color_opacity="1"
column_shadow="none" column_border_radius="none" column_link_target="_self" width="1/2"
tablet_width_inherit="default" overlay_strength="0.3" column_border_width="none" column_border_style="solid"
bg_image_animation="none"][image_with_animation image_url="159640" alignment="center" animation="Fade In"
hover_animation="none" border_radius="none" box_shadow="none" image_loading="default" max_width="100%"
max_width_mobile="default"][/vc_column_inner][vc_column_inner column_padding="no-extra-padding"
column_padding_position="all" background_color_opacity="1" background_hover_color_opacity="1"
column_shadow="none" column_border_radius="none" column_link_target="_self" width="1/2"
tablet_width_inherit="default" overlay_strength="0.3" column_border_width="none" column_border_style="solid"
bg_image_animation="none"][image_with_animation image_url="159646" alignment="center" animation="Fade In"
hover_animation="none" border_radius="none" box_shadow="none" image_loading="default" max_width="100%"
max_width_mobile="default"][/vc_column_inner][vc_row_inner][vc_column_text]Tipo: Loftrex Longitud : 20 "Micragem: 50 micrones[/vc_column_text][vc_column_text]

- **Cartuchos Matrikx**

[/vc_column_text][image_with_animation image_url="159689" alignment="center" animation="Fade In" hover_animation="none" border_radius="none" box_shadow="none" image_loading="default" max_width="100%" max_width_mobile="default"] [vc_column_text]Referencia típica : 01-250-125-975

Tipo de matriz OD: 2,50 "Longitud Longitud: 9,75" [/vc_column_text][vc_column_text]

- [Cartuchos Osmonics](#)

[/vc_column_text][image_with_animation image_url="158933" alignment="center" animation="Fade In" hover_animation="none" border_radius="none" box_shadow="none" image_loading="default" max_width="100%" max_width_mobile="default"] [vc_column_text]Referencia típica : PX-05-10

Tipo: Purtrex Micure: 5 mcr Longitud: 10 " [/vc_column_text][vc_column_text]

- [Cartuchos Oil-Block](#)

[/vc_column_text][image_with_animation image_url="158847" alignment="center" animation="Fade In" hover_animation="none" border_radius="none" box_shadow="none" image_loading="default" max_width="100%" max_width_mobile="default"] [vc_column_text]Temas relacionados :

Capacidad de retención de suciedad (Capacidade de retenção da sujidade)

Potencial Zeta (Potencial Zeta)

Consulte también nuestras posibilidades de filtración alternativas

fuentes: manual de filtros y filtración, 3ª edición, tecnología avanzada elsevier

Haga clic aquí para ver una comparación entre los filtros de cartucho y los filtros de bolsa.

Encuentre más información sobre filtros de sedimentos.

Consulte también nuestras posibilidades de filtración alternativas

[/vc_column_text][/vc_column][vc_row]

INFORMACIÓN ADICIONAL

COTECNO