

## FILTRO ZERO



**SKU:** N / A | **Categorías:** [Prensa de filtro](#) |

## DESCRIPCIÓN DEL PRODUCTO

[vc\_row type="in\_container" full\_screen\_row\_position="middle" column\_margin="default" scene\_position="center" text\_color="dark" text\_align="left" overlay\_strength="0.3" shape\_divider\_position="bottom" bg\_image\_animation="none"][vc\_column column\_padding="no-extra-padding" column\_padding\_position="all" background\_color\_opacity="1" background\_hover\_color\_opacity="1" column\_link\_target="\_self" column\_shadow="none" column\_border\_radius="none" width="1/1" tablet\_width\_inherit="default" tablet\_text\_alignment="default" phone\_text\_alignment="default" overlay\_strength="0.3" column\_border\_width="none" column\_border\_style="solid" bg\_image\_animation="none"][tabbed\_section style="default" alignment="left" spacing="default" tab\_color="Accent-Color"][/tabbed\_section][vc\_column\_text]

### Especificaciones Técnicas

[/vc\_column\_text][vc\_column\_text]

Código del Producto	Modelo	Dia de placas (pulgadas)	No. de placas	Alturas de placas (mm)	Área de filtración (Sq. Mtr.)	Capacidad de retención de pasteles (rf ^)	Tasa de flujo ~ (ltrs / hr)	Tamaño de la bomba	Motor (hp)
B-01-24-19-01-0101	BellFilPreZer-84	8	4	25	0.132	2.5	300	0,5 "	1.0
B-01-24-19-01-0102	BellFilPreZer-86	8	6	25	0.198	3.9	400	0,5 "	1.0
B-01-24-19-01-0103	BellFilPreZer-88	8	8	25	0.254	4.95	500	0,5 "	1.0
B-01-24-19-01-0104	BellFilPreZer-144	14	4	38	0.378	12.9	700	1.0 "	2.0
B-01-24-19-01-0105	BellFilPreZer-146	14	6	38	0.567	17.2	1200	1.0 "	2.0
B-01-24-19-01-0106	BellFilPreZer-148	14	8	38	0.756	23.5	1600	1.0 "	2.0
B-01-24-19-01-0107	BellFilPreZer-1410	14	10	38	0.924	27.5	2000	1.0 "	2.0
B-01-24-19-01-0108	BellFilPreZer-1412	14	12	38	1.156	29.95	2300	1.0 "	2.0
B-01-24-19-01-0109	BellFilPreZer-188	18	8	50	1.27	47	2500	1,5 "	3
B-01-24-19-01-0110	BellFilPreZer-1810	18	10	50	1.62	54.2	3200	1,5 "	3
B-01-24-19-01-0111	BellFilPreZer-1812	18	12	50	1.842	67.2	4000	1,5 "	3
B-01-24-19-01-0112	BellFilPreZer-1815	18	15	25	2.27	37.5	5000	1,5 "	3
B-01-24-19-01-0113	BellFilPreZer-1818A	18	18	25	2.72	50	5500	1,5 "	3
B-01-24-19-01-0114	BellFilPreZer-1818B	18	18	50	2.77	100	5500	1,5 "	3
B-01-24-19-01-0115	BellFilPreZer-1823	18	23	25	3.45	57	6800	1,5 "	3
B-01-24-19-01-0116	BellFilPreZer-2412	24	12	50	3.37	110	6700	2,0 "	5
B-01-24-19-01-0117	BellFilPreZer-2415	24	15	50	4.21	123	7800	2,0 "	5
B-01-24-19-01-0118	BellFilPreZer-2418	24	18	38	5.04	130	10000	2,0 "	5
B-01-24-19-01-0119	BellFilPreZer-2423	24	23	38	6.34	165	12500	2,0 "	5
B-01-24-19-01-0120	BellFilPreZer-337	33	7	38	4.2	N / A	8000	2,5 "	7.5
B-01-24-19-01-0121	BellFilPreZer-3310	33	10	38	5.6	N / A	11000	2,5 "	7.5
B-01-24-19-01-0122	BellFilPreZer-3314	33	14	38	7.5	N / A	15000	2,5 "	7.5
B-01-24-19-01-0123	BellFilPreZer-3323	33	23	38	14.0	N / A	25000	2,5 "	7.5

[/vc\_column\_text][/vc\_column][/vc\_row]

## INFORMACIÓN ADICIONAL

COTECNO