

## FILTROS LENNBAG



**SKU:** N / A | **Categorías:** [Filtros LenNBAG](#), [Lenntech](#) |

## DESCRIPCIÓN DEL PRODUCTO

[vc\_row type="in\_container" full\_screen\_row\_position="middle" column\_margin="default" scene\_position="center" text\_color="dark" text\_align="left" overlay\_strength="0.3" shape\_divider\_position="bottom" bg\_image\_animation="none"][vc\_column column\_padding="no-extra-padding" column\_padding\_position="all" background\_color\_opacity="1" background\_hover\_color\_opacity="1" column\_link\_target="\_self" column\_shadow="none" column\_border\_radius="none" width="1/1" tablet\_width\_inherit="default" tablet\_text\_alignment="default" phone\_text\_alignment="default" overlay\_strength="0.3" column\_border\_width="none" column\_border\_style="solid" bg\_image\_animation="none"][tabbed\_section style="default" alignment="left" spacing="default" tab\_color="Accent-Color"][/tabbed\_section][vc\_row\_inner column\_margin="default" text\_align="left"][vc\_column\_inner column\_padding="no-extra-padding" column\_padding\_position="all" background\_color\_opacity="1" background\_hover\_color\_opacity="1" column\_shadow="none" column\_border\_radius="none" column\_link\_target="\_self" width="1/3" tablet\_width\_inherit="default" overlay\_strength="0.3" column\_border\_width="none" column\_border\_style="solid" bg\_image\_animation="none"][vc\_column\_text]

### Bolsa de filtro de alto rendimiento

- [LennBag HE](#)

[/vc\_column\_text][vc\_column\_inner][vc\_column\_inner column\_padding="no-extra-padding" column\_padding\_position="all" background\_color\_opacity="1" background\_hover\_color\_opacity="1" column\_shadow="none" column\_border\_radius="none" column\_link\_target="\_self" width="1/3" tablet\_width\_inherit="default" overlay\_strength="0.3" column\_border\_width="none" column\_border\_style="solid" bg\_image\_animation="none"][vc\_column\_text]**Bolsa de filtro de monofilamento**

- [LennBag NMO - PEMO - POMO - T](#)

[/vc\_column\_text][vc\_column\_inner][vc\_column\_inner column\_padding="no-extra-padding" column\_padding\_position="all" background\_color\_opacity="1" background\_hover\_color\_opacity="1" column\_shadow="none" column\_border\_radius="none" column\_link\_target="\_self" width="1/3" tablet\_width\_inherit="default" overlay\_strength="0.3" column\_border\_width="none" column\_border\_style="solid" bg\_image\_animation="none"][image\_with\_animation image\_url="158815" alignment="center" animation="Fade In" hover\_animation="none" border\_radius="none" box\_shadow="none" image\_loading="default" max\_width="100%" max\_width\_mobile="default"][/vc\_column\_inner][vc\_row\_inner][vc\_row\_inner column\_margin="default" text\_align="left"][vc\_column\_inner column\_padding="no-extra-padding" column\_padding\_position="all" background\_color\_opacity="1" background\_hover\_color\_opacity="1" column\_shadow="none" column\_border\_radius="none" column\_link\_target="\_self" width="1/3" tablet\_width\_inherit="default" overlay\_strength="0.3" column\_border\_width="none" column\_border\_style="solid" bg\_image\_animation="none"][vc\_column\_text]**Bolsa de filtro de fieltro de aguja**

### [LennBag PO - PE - N - PTFE - PPS - HT](#)

[/vc\_column\_text][vc\_column\_inner][vc\_column\_inner column\_padding="no-extra-padding" column\_padding\_position="all" background\_color\_opacity="1" background\_hover\_color\_opacity="1" column\_shadow="none" column\_border\_radius="none" column\_link\_target="\_self" width="1/3" tablet\_width\_inherit="default" overlay\_strength="0.3" column\_border\_width="none" column\_border\_style="solid" bg\_image\_animation="none"][vc\_column\_text]**Bolsa de filtro de alta eficiencia**

- [LennBag PP95](#)

[/vc\_column\_text][vc\_column\_inner][vc\_column\_inner column\_padding="no-extra-padding" column\_padding\_position="all" background\_color\_opacity="1" background\_hover\_color\_opacity="1" column\_shadow="none"

column\_border\_radius="none" column\_link\_target="\_self" width="1/3" tablet\_width\_inherit="default"  
overlay\_strength="0.3" column\_border\_width="none" column\_border\_style="solid"  
bg\_image\_animation="none"]vc\_column\_text] **Bolsa de filtro de alta eficiencia**

- [LennBag PP95](#)

[/vc\_column\_text][vc\_column\_inner][vc\_row\_inner]

[vc\_column\_text]

### **Descripción General**

- [LennHFP](#)
- [Carcasas LennBag](#)
- [Descripción General De Los Filtros Lennbag](#)

[/vc\_column\_text][vc\_column][vc\_row]

COTECNO

## INFORMACIÓN ADICIONAL

COTECNO