

FILTROS PARKER



SKU: N / A | **Categorías:** [Filtros de sedimentos](#), [Filtros Parker](#) |

DESCRIPCIÓN DEL PRODUCTO

[vc_row type="in_container" full_screen_row_position="middle" column_margin="default" scene_position="center" text_color="dark" text_align="left" overlay_strength="0.3" shape_divider_position="bottom" bg_image_animation="none"][vc_column column_padding="no-extra-padding" column_padding_position="all" background_color_opacity="1" background_hover_color_opacity="1" column_link_target="_self" column_shadow="none" column_border_radius="none" width="1/1" tablet_width_inherit="default" tablet_text_alignment="default" phone_text_alignment="default" overlay_strength="0.3" column_border_width="none" column_border_style="solid" bg_image_animation="none"][tabbed_section style="default" alignment="left" spacing="default" tab_color="Accent-Color"][/tabbed_section][vc_row_inner column_margin="default" text_align="left"][vc_column_inner column_padding="no-extra-padding" column_padding_position="all" background_color_opacity="1" background_hover_color_opacity="1" column_shadow="none" column_border_radius="none" column_link_target="_self" width="1/2" tablet_width_inherit="default" overlay_strength="0.3" column_border_width="none" column_border_style="solid" bg_image_animation="none"][vc_column_text]

Bolsas de filtro

- [Descripción general de las bolsas de filtro](#)
- [Bolsas de filtro Fulflo](#)
- [Coladores de cesta Fulflo](#)

Filtros de cartucho de carbón

[/vc_column_text][vc_column_inner][vc_column_inner column_padding="no-extra-padding" column_padding_position="all" background_color_opacity="1" background_hover_color_opacity="1" column_shadow="none" column_border_radius="none" column_link_target="_self" width="1/2" tablet_width_inherit="default" overlay_strength="0.3" column_border_width="none" column_border_style="solid" bg_image_animation="none"][/vc_column_inner][vc_row_inner][vc_row_inner column_margin="default" text_align="left"][vc_column_inner column_padding="no-extra-padding" column_padding_position="all" background_color_opacity="1" background_hover_color_opacity="1" column_shadow="none" column_border_radius="none" column_link_target="_self" width="1/2" tablet_width_inherit="default" overlay_strength="0.3" column_border_width="none" column_border_style="solid" bg_image_animation="none"][/vc_column_text]

- [Cartucho de filtro CAROFLO](#)
- [Cartucho de filtro CAROFLO MX](#)

Cartuchos de filtro de profundidad

- [Cartucho de filtro Fulllo DoraBond](#)
- [Cartucho de filtro Fulflo EcoBond](#)
- [Cartucho de filtro de sonda de flores](#)
- [Cartucho de filtro de panal Fulflo](#)

[/vc_column_text][vc_column_inner][vc_column_inner column_padding="no-extra-padding" column_padding_position="all" background_color_opacity="1" background_hover_color_opacity="1" column_shadow="none" column_border_radius="none" column_link_target="_self" width="1/2" tablet_width_inherit="default" overlay_strength="0.3" column_border_width="none" column_border_style="solid" bg_image_animation="none"][image_with_animation image_url="159284" alignment="center" animation="Fade In" hover_animation="none" border_radius="none" box_shadow="none" image_loading="default" max_width="100%"]

max_width_mobile="default"][/vc_column_inner][[/vc_row_inner][[/vc_column][[/vc_row]

COTECNO

INFORMACIÓN ADICIONAL

COTECNO