

FILTROS PENTAIR



SKU: N / A | **Categorías:** [Filtros de sedimentos](#), [Filtros Pentair](#) |

DESCRIPCIÓN DEL PRODUCTO

```
[vc_row type="in_container" full_screen_row_position="middle" column_margin="default" scene_position="center" text_color="dark" text_align="left" overlay_strength="0.3" shape_divider_position="bottom" bg_image_animation="none"][vc_column column_padding="no-extra-padding" column_padding_position="all" background_color_opacity="1" background_hover_color_opacity="1" column_link_target="_self" column_shadow="none" column_border_radius="none" width="1/1" tablet_width_inherit="default" tablet_text_alignment="default" phone_text_alignment="default" overlay_strength="0.3" column_border_width="none" column_border_style="solid" bg_image_animation="none"][tabbed_section style="default" alignment="left" spacing="default" tab_color="Accent-Color"][/tabbed_section][vc_column_text]
```

Seleccione aquí su preselección

```
[/vc_column_text][vc_row_inner column_margin="default" text_align="left"][vc_column_inner column_padding="no-extra-padding" column_padding_position="all" background_color_opacity="1" background_hover_color_opacity="1" column_shadow="none" column_border_radius="none" column_link_target="_self" width="1/3" tablet_width_inherit="default" overlay_strength="0.3" column_border_width="none" column_border_style="solid" bg_image_animation="none"][vc_column_text]
```

- Cartucho de filtro industrial
- Cartucho de carbón industrial
- Carcasas de cartuchos y bolsas de acero inoxidable

```
[/vc_column_text][vc_column_inner][vc_column_inner column_padding="no-extra-padding" column_padding_position="all" background_color_opacity="1" background_hover_color_opacity="1" column_shadow="none" column_border_radius="none" column_link_target="_self" width="1/3" tablet_width_inherit="default" overlay_strength="0.3" column_border_width="none" column_border_style="solid" bg_image_animation="none"][vc_column_text]
```

- Bolsas de filtro industriales
- Cartuchos Aqualine industriales
- Resumen de todos los filtros

```
[/vc_column_text][vc_column_inner][vc_column_inner column_padding="no-extra-padding" column_padding_position="all" background_color_opacity="1" background_hover_color_opacity="1" column_shadow="none" column_border_radius="none" column_link_target="_self" width="1/3" tablet_width_inherit="default" overlay_strength="0.3" column_border_width="none" column_border_style="solid" bg_image_animation="none"][vc_column_text]
```

- Carcasas de cartuchos de líquido
- Carcasas para bolsas de líquidos

```
[/vc_column_text][vc_column_inner][vc_row_inner][vc_column_text]
```

Cartuchos de filtro industrial Pentair

```
[/vc_column_text][vc_row_inner column_margin="default" text_align="left"][vc_column_inner column_padding="no-extra-padding" column_padding_position="all" background_color_opacity="1" background_hover_color_opacity="1" column_shadow="none" column_border_radius="none" column_link_target="_self" width="1/3" tablet_width_inherit="default" overlay_strength="0.3" column_border_width="none" column_border_style="solid" bg_image_animation="none"][vc_column_text]
```

- Serie Cellflex

- Serie Coreflex
- Serie Pentaflex
- Serie Pureflex
- Serie Resflex
- Serie Steelflex
- Serie Stringflex
- Serie Teflex
- Serie Versaflex GD
- Serie Versaflex HE
- Serie Versaflex MB
- WP
- WP BB
- WPX BB
- Serie DXF
- Serie S-1

```
[/vc_column_text][vc_column_inner][vc_column_inner column_padding="no-extra-padding" column_padding_position="all" background_color_opacity="1" background_hover_color_opacity="1" column_shadow="none" column_border_radius="none" column_link_target="_self" width="1/3" tablet_width_inherit="default" overlay_strength="0.3" column_border_width="none" column_border_style="solid" bg_image_animation="none"][image_with_animation image_url="159305" alignment="center" animation="Fade In" hover_animation="none" border_radius="none" box_shadow="none" image_loading="default" max_width="100%" max_width_mobile="default"][/vc_column_inner][vc_column_inner column_padding="no-extra-padding" column_padding_position="all" background_color_opacity="1" background_hover_color_opacity="1" column_shadow="none" column_border_radius="none" column_link_target="_self" width="1/3" tablet_width_inherit="default" overlay_strength="0.3" column_border_width="none" column_border_style="solid" bg_image_animation="none"][vc_column_text]
```

- Serie P
- Serie DGD
- Serie CW
- Serie R
- CRE-1 Cerámica
- Serie WS
- Serie PCC
- RFFE-10/20 BB
- PCF
- Serie Polydepth
- Serie ECP
- Polyval
- Polyval HE
- SHG
- SHP

```
[/vc_column_text][/vc_column_inner][/vc_row_inner]
```

```
[vc_column_text]
```

Cartuchos de carbono industriales Pentair

```
[/vc_column_text][vc_row_inner column_margin="default" text_align="left"][vc_column_inner column_padding="no-extra-padding" column_padding_position="all" background_color_opacity="1" background_hover_color_opacity="1" column_shadow="none" column_border_radius="none" column_link_target="_self" width="1/3"
```

tablet_width_inherit="default" overlay_strength="0.3" column_border_width="none" column_border_style="solid" bg_image_animation="none"]vc_column_text]

- [Carbflex CFB](#)
- [Carbflex CFB - 10](#)
- [Carbflex CFB - PB10](#)
- [Carbflex CFB - Plus](#)
- [Carbflex GAC](#)
- [Carbflex OAC](#)
- [C-155](#)
- [C-234](#)
- [C-245](#)
- [C-246](#)
- [C-8](#)
- [SCBC-10](#)
- [NCP](#)

[/vc_column_text][vc_column_inner][vc_column_inner column_padding="no-extra-padding" column_padding_position="all" background_color_opacity="1" background_hover_color_opacity="1" column_shadow="none" column_border_radius="none" column_link_target="_self" width="1/3" tablet_width_inherit="default" overlay_strength="0.3" column_border_width="none" column_border_style="solid" bg_image_animation="none"][image_with_animation image_url="159308" alignment="center" animation="Fade In" hover_animation="none" border_radius="none" box_shadow="none" image_loading="default" max_width="100%" max_width_mobile="default"][/vc_column_inner][vc_column_inner column_padding="no-extra-padding" column_padding_position="all" background_color_opacity="1" background_hover_color_opacity="1" column_shadow="none" column_border_radius="none" column_link_target="_self" width="1/3" tablet_width_inherit="default" overlay_strength="0.3" column_border_width="none" column_border_style="solid" bg_image_animation="none"]vc_column_text]

- [GAC](#)
- [SGAC](#)
- [TSGAC](#)
- [CC](#)
- [RFC](#)
- [EP](#)
- [EPM](#)
- [CBC](#)
- [A base de coco](#)
- [ChlorPlus](#)
- [Serie ELPC](#)
- [FloPlus](#)
- [UDS / DBC](#)

[/vc_column_text][/vc_column_inner][/vc_row_inner]

[vc_row_inner column_margin="default" text_align="left"]vc_column_inner column_padding="no-extra-padding" column_padding_position="all" background_color_opacity="1" background_hover_color_opacity="1" column_shadow="none" column_border_radius="none" column_link_target="_self" width="1/3" tablet_width_inherit="default" overlay_strength="0.3" column_border_width="none" column_border_style="solid" bg_image_animation="none"]vc_column_text]**Bolsas de filtro industriales Pentair**

- [Bolsas filtrantes BP, BPHE y BN](#)
- [Bolsas de filtro de líquido](#)

- [Bolsas de filtro de la serie MHP](#)
- [Bolsas de filtro plisadas](#)

```
[/vc_column_text][/vc_column_inner][vc_column_inner column_padding="no-extra-padding" column_padding_position="all" background_color_opacity="1" background_hover_color_opacity="1" column_shadow="none" column_border_radius="none" column_link_target="_self" width="1/3" tablet_width_inherit="default" overlay_strength="0.3" column_border_width="none" column_border_style="solid" bg_image_animation="none"][image_with_animation image_url="159309" alignment="center" animation="Fade In" hover_animation="none" border_radius="none" box_shadow="none" image_loading="default" max_width="100%" max_width_mobile="default"][/vc_column_inner][vc_column_inner column_padding="no-extra-padding" column_padding_position="all" background_color_opacity="1" background_hover_color_opacity="1" column_shadow="none" column_border_radius="none" column_link_target="_self" width="1/3" tablet_width_inherit="default" overlay_strength="0.3" column_border_width="none" column_border_style="solid" bg_image_animation="none"][image_with_animation image_url="159310" alignment="center" animation="Fade In" hover_animation="none" border_radius="none" box_shadow="none" image_loading="default" max_width="100%" max_width_mobile="default"][/vc_column_inner][/vc_row_inner]
```

```
[vc_row_inner column_margin="default" text_align="left"][vc_column_inner column_padding="no-extra-padding" column_padding_position="all" background_color_opacity="1" background_hover_color_opacity="1" column_shadow="none" column_border_radius="none" column_link_target="_self" width="1/2" tablet_width_inherit="default" overlay_strength="0.3" column_border_width="none" column_border_style="solid" bg_image_animation="none"][/vc_column_text]
```

- AL.6-60B
- AL1.2-60B
- AL2-60B
- [AL05-60B](#)
- [AL10-60B](#)
- [AL20-60B](#)
- AL40-60B
- AL70-60B
- AL100-60B
- ALN20-60B

```
[/vc_column_text][/vc_column_inner][vc_column_inner column_padding="no-extra-padding" column_padding_position="all" background_color_opacity="1" background_hover_color_opacity="1" column_shadow="none" column_border_radius="none" column_link_target="_self" width="1/2" tablet_width_inherit="default" overlay_strength="0.3" column_border_width="none" column_border_style="solid" bg_image_animation="none"][/vc_column_text]
```

- AQ8-60B
- AQ8-60-B-1-CB
- [80AQ15-60 no codificado](#)
- [80CF15-60 no codificado](#)
- [Cumple con el código 80CF15-60](#)
- [Cumple con el código 80CF30-60](#)
- [Información general de Aqualine](#)

```
[/vc_column_text][/vc_column_inner][/vc_row_inner][vc_column_text]
```

Carcasas de cartuchos de líquido Pentair

```
[/vc_column_text][vc_row_inner column_margin="default" text_align="left"][vc_column_inner column_padding="no-extra-padding" column_padding_position="all" background_color_opacity="1" background_hover_color_opacity="1"
```

column_shadow="none" column_border_radius="none" column_link_target="_self" width="1/3"
tablet_width_inherit="default" overlay_strength="0.3" column_border_width="none" column_border_style="solid"
bg_image_animation="none"]][vc_column_text]

- [3G de línea delgada](#)
- [Polipropileno All Nature](#)
- [Azul grande / Claro grande](#)
- [C44 Individual](#)
- [C66 3 - Redondo](#)
- [C88 6 - Ronda](#)
- [E - Serie](#)
- [Alta temperatura](#)

[/vc_column_text][vc_column_inner][vc_column_inner column_padding="no-extra-padding" column_padding_position="all"
background_color_opacity="1" background_hover_color_opacity="1" column_shadow="none"
column_border_radius="none" column_link_target="_self" width="1/3" tablet_width_inherit="default"
overlay_strength="0.3" column_border_width="none" column_border_style="solid"
bg_image_animation="none"]][image_with_animation image_url="159311" alignment="center" animation="Fade In"
hover_animation="none" border_radius="none" box_shadow="none" image_loading="default" max_width="100%"
max_width_mobile="default"]][vc_column_inner][vc_column_inner column_padding="no-extra-padding"
column_padding_position="all" background_color_opacity="1" background_hover_color_opacity="1"
column_shadow="none" column_border_radius="none" column_link_target="_self" width="1/3"
tablet_width_inherit="default" overlay_strength="0.3" column_border_width="none" column_border_style="solid"
bg_image_animation="none"]][vc_column_text]

- [Coladores en línea](#)
- [Multi - Ronda](#)
- [ST - Serie](#)
- [MPST](#)
- [Gorra plana Slim-line](#)

[/vc_column_text][/vc_column_inner][/vc_row_inner][vc_column_text]

Pentair Carcasas para bolsas de líquidos

[/vc_column_text][vc_row_inner column_margin="default" text_align="left"]][vc_column_inner column_padding="no-extra-
padding" column_padding_position="all" background_color_opacity="1" background_hover_color_opacity="1"
column_shadow="none" column_border_radius="none" column_link_target="_self" width="1/3"
tablet_width_inherit="default" overlay_strength="0.3" column_border_width="none" column_border_style="solid"
bg_image_animation="none"]][vc_column_text]

- [L44 Individual](#)
- [L66 Individual](#)
- [L88 Individual](#)
- [T88 Sencillo](#)
- [OEM M88 100 PSI](#)

[/vc_column_text][/vc_column_inner][vc_column_inner column_padding="no-extra-padding" column_padding_position="all"
background_color_opacity="1" background_hover_color_opacity="1" column_shadow="none"
column_border_radius="none" column_link_target="_self" width="1/3" tablet_width_inherit="default"
overlay_strength="0.3" column_border_width="none" column_border_style="solid"
bg_image_animation="none"]][image_with_animation image_url="159312" alignment="center" animation="Fade In"
hover_animation="none" border_radius="none" box_shadow="none" image_loading="default" max_width="100%"
max_width_mobile="default"]][vc_column_inner][vc_column_inner column_padding="no-extra-padding"

column_padding_position="all" background_color_opacity="1" background_hover_color_opacity="1"
column_shadow="none" column_border_radius="none" column_link_target="_self" width="1/3"
tablet_width_inherit="default" overlay_strength="0.3" column_border_width="none" column_border_style="solid"
bg_image_animation="none"]vc_column_text]

- [Diversa - Flujo](#)
- [Serie Multi - Ronda](#)
- [Dúplex](#)
- [Serie PBH](#)
- [Capacidad Twin L882](#)

[/vc_column_text][vc_column_inner][vc_row_inner]

[vc_column_text]

Carcasas y cartuchos de acero inoxidable Pentair para bolsas

[/vc_column_text][vc_column_text]

- [CFHC](#)
- [BFHF](#)

[/vc_column_text][vc_column][vc_row]

INFORMACIÓN ADICIONAL

COTECNO