

GABINETE DE TRABAJO DE SUMINISTRO DE AIRE/ MEDICO - BELLCABSUMMED-1030A



Gabinete de flujo laminar de suministro de aire vertical

- 1.Acero inoxidable304
- 2.Aire vertical
- 3.Clase 100
- 4.Médico

SKU: B-01-12-04-000201 | **Categorías:** [Gabinete de trabajo de suministro de aire](#) |

GALERÍA DE IMÁGENES



DESCRIPCIÓN DEL PRODUCTO

Características del producto

1. Adopta el sistema de puerta deslizante de posicionamiento arbitrario.
2. La carcasa está soldada por placas laminadas en frío, la superficie está rociada electrostáticamente, y la superficie de trabajo es de acero inoxidable cepillado SUS304, que es resistente a la corrosión y fácil de limpiar.
3. Los sistemas de iluminación y esterilización están interconectados de forma segura, y hay una función de sincronización de la luz ultravioleta.
4. 4. Interfaz de control LCD con pantalla digital, diseño más fácil de usar.

Product details



High efficiency filter

HEPA Filter ensures a clean environment in the work area.

Fluorescent lamp & UV lamp

Equipped with high-brightness fluorescent lamps, safety interlocking of lighting and sterilization systems.



Socket

Four types of sockets are available



European standard socket



American standard socket



Chinese standard socket



British standard socket




Socket (Four options)


The working area is equipped with sockets (four options are available) to facilitate the experiment plug-in needs.

All steel material

The product structure is firmer and the appearance is more beautiful.



Product introduction



Laminar flow cabinet

- The material of the work area is 304 stainless steel.
- Arbitrary positioning door shifting system
- Digital display LIQUID crystal control interface




LCD control panel



Digital display control panel, three-speed adjustable for fast, medium and slow, more humanized design.

Copper core motor

The motor has strong power, low heat generation, low noise, energy-saving and power-saving.



Working area

The material of the work area is 304 stainless steel, Resistant to corrosion and easy to clean.



Universal wheel

The base is equipped with universal wheels to facilitate the movement of the clean bench.



INFORMACIÓN ADICIONAL

COTECNO