

GENERADOR PORTÁTIL DE OZONO PARA EL TRATAMIENTO DE AIRE



SKU: B-01-12-13-000100 | **Categorías:** [Generador de Ozono](#) |

GALERÍA DE IMÁGENES

Product introduction



Ozone Generator

— Fast speed / Good effect / Wide range —

- ⊗ Production workshop disinfection
- ⊗ Farm disinfection
- ⊗ Cold storage, storage
- ⊗ Food factory disinfection



DESCRIPCIÓN DEL PRODUCTO

Generador Portátil De Ozono Para El Tratamiento De Aire

- (1) Desinfección de habitaciones de hotel, desinfección de automóviles, desinfección de oficinas, desinfección de hoteles, etc.
- (2) Esterilización en el taller de producción, desinfección de sábanas, desinfección de salas, desinfección de jardines de infancia escolares, etc.
- (3) Cultivo de hongos para prevenir infecciones.
- (4) esterilizar y mantener fresco en las plantas de procesamiento de alimentos para eliminar el olor

Especificaciones Tecnicas

Codigo del Producto

B-01-12-13-000100

Modelo	BellGenOzoAirPor
nombre del producto	Generador de ozono
Tamaño del producto (L*W*H mm)	275*185*150
Tamaño del embalaje (L*W*H mm)	332*233*232
Producción de ozono (g/h)	5
Peso bruto (kg)	3.2
Concentración de ozono (PPM)	15-40
Consumo de energía de ozono (W)	60
La potencia de entrada	AC 110-220V/50-60HZ
Manera de enfriamiento	Aire acondicionado
Condiciones del entorno de trabajo	Temperatura ambiente <45C, RH≤80 %, estrictamente prohibido en lugares inflamables y explosivos
Usando	fuentes de aire
Cuerpo material	Revestimiento de placa de hierro
Color del cuerpo	Naranja, beis, negro
Modo de operación	Pantalla táctil + control remoto

Ozone Generator

— Fast speed / Good effect / Wide range —

- Production workshop disinfection
- Farm disinfection
- Cold storage, storage
- Food factory disinfection



Range of application



➤ Factory workshop

The ozone can carry on the ozone sterilization to the workshop, can improve the hygienic quality.

➤ Food processing plant

Ozone can disinfect the surface of food and inhibit the growth of mould.



➤ Toiletries workshop

Ozone can be used to sterilize the production equipment of filling container and packaging material.

Schools, kindergartens

Toys, books, cushions, etc. For children. No secondary pollution after disinfection to protect the health of Children.



Office space of Enterprise

The company's Office space personnel flow is larger, can be a regular daily ozone disinfection prevention.

Internet cafe, KTV

Ozone disinfection every day for 1 hour to ensure a good space environment experience, effective prevention of bacterial transmission.







Product introduction



Product analysis

Touch screen

Switch on the power and touch the on key lightly  When the equipment starts to work, the display shows the countdown working time. If the working time needs to be adjusted, please touch it lightly  or  After setting the completion time, press  key.




The shell

Iron plate spray appearance, fashion appearance, waterproof and moistureproof, anti-oxidation, anti-fouling ability, easy to clean, to deal with harsh environment, commercial disinfection service life longer.



Double ball bearing cooling fan

This product USES double ball bearing cooling fan, high speed and large air volume to ensure that the heat dissipation of the heating elements inside the machine is good, low ozone concentration attenuation rate, long time use can still ensure adequate ozone production, concentration standard.



Product to film



INFORMACIÓN ADICIONAL

Medición de ppm máxima

[40](#)

COTECNO