

KITS DE CHASIS ASTM CHASE



[vc_row][vc_column][vc_column_text]se utilizan para moldear placas de prueba de polietileno, que incluyen (2) placas de respaldo de aluminio y 50 hojas de Mylar[/vc_column_text][vc_table][14px;align-center]Numero%20de%20catalogo,[14px;align-center]Descripci%C3%B3n,[14px;align-center]Dimensiones%20de%20muestra,[14px;align-center]Material|[14px;align-center]4079,[14px;align-center]ASTM%20Chase%20Frame%20Kit,[14px;align-center]4%20%22x%204%22%20x%201%2F8%20%22,[14px;align-center]Acero%20recubierto%20de%20tefl%C3%B3n|[14px;align-center]4080,[14px;align-center]ASTM%20Chase%20Frame%20Kit,[14px;align-center]4%20%22x%204%22%20x%201%2F8%20%22,[14px;align-center]Acero%20inoxidable|[14px;align-center]4081,[14px;align-center]ASTM%20Chase%20Frame%20Kit,[14px;align-center]4%20%22x%204%22%20x%201%2F8%20%22,[14px;align-center]Lat%C3%B3n|[14px;align-center]4082,[14px;align-center]ASTM%20Chase%20Frame%20Kit,[14px;align-center]6%20%22x%206%22%20x%201%2F8%20%22,[14px;align-center]Acero%20recubierto%20de%20tefl%C3%B3n|[14px;align-center]4083,[14px;align-center]ASTM%20Chase%20Frame%20Kit,[14px;align-center]6%20%22x%206%22%20x%201%2F8%20%22,[14px;align-center]Acero%20inoxidable|[14px;align-center]4084,[14px;align-center]ASTM%20Chase%20Frame%20Kit,[14px;align-center]6%20%22x%206%22%20x%201%2F8%20%22,[14px;align-center]Lat%C3%B3n|[14px;align-center]4085,[14px;align-center]ASTM%20Chase%20Frame%20Kit,[14px;align-center]8%20%22x%208%22%20x%201%2F8%20%22,[14px;align-center]Acero%20recubierto%20de%20tefl%C3%B3n|[14px;align-center]4086,[14px;align-center]ASTM%20Chase%20Frame%20Kit,[14px;align-center]8%20%22x%208%22%20x%201%2F8%20%22,[14px;align-center]Acero%20inoxidable|[14px;align-center]4087,[14px;align-center]ASTM%20Chase%20Frame%20Kit,[14px;align-center]8%20%22x%208%22%20x%201%2F8%20%22,[14px;align-center]Lat%C3%B3n|[14px;align-center]4161,[14px;align-center](100)%20Hojas%20de%20Mylar%20para%20moldes%20de%206%20%22x%206%22,[14px;align-center]4%20%22x%204%22,[14px;align-center]Mylar|[14px;align-center]4162,[14px;align-center](100)%20Hojas%20de%20Mylar%20para%20moldes%20de%208%20%22x%208%22,[14px;align-center]6%20%22x%206%22,[14px;align-center]Mylar|[14px;align-center]4163,[14px;align-center](100)%20Hojas%20de%20Mylar%20para%20moldes%20de%2010%20%22x%2010%22,[14px;align-center]8%20%22x%208%22,[14px;align-center]Mylar[/vc_table][vc_column][vc_row]

SKU: N / A | **Categorías:** [ASTM](#) / [Moldes especiales](#) |

COTECNO

INFORMACIÓN ADICIONAL

COTECNO