

LOCALIZADOR SEEKTECH SR-60



SKU: N / A | **Categorías:** [cañerías](#), [Diagnóstico](#), [Ensayos no destructivos](#), [Inspección Y Localización](#), [Servicios públicos](#), [tuberías y vacíos](#) | **Etiquetas:** [Ridgid](#)

GALERÍA DE IMÁGENES



DESCRIPCIÓN DEL PRODUCTO

Localizador SeekTech SR-60

Para contar con el receptor más rápido, sencillo y versátil del mercado.

Escoja el localizador SR-60 para localizaciones rápidas y fiables, incluso en las condiciones más desfavorables (conductores deficientes, suelos en mal estado, puestas a tierra defectuosas, etc.).

```
[vc_row type="in_container" full_screen_row_position="middle" scene_position="center" text_color="dark" text_align="left" overlay_strength="0.3"][vc_column column_padding="no-extra-padding" column_padding_position="all" background_color_opacity="1" background_hover_color_opacity="1" column_shadow="none" width="1/1" tablet_text_alignment="default" phone_text_alignment="default" column_border_width="none" column_border_style="solid"]
```

```
[/vc_column][vc_row][vc_row type="in_container" full_screen_row_position="middle" scene_position="center" text_color="dark" text_align="left" overlay_strength="0.3"][vc_column column_padding="no-extra-padding" column_padding_position="all" background_color_opacity="1" background_hover_color_opacity="1" column_shadow="none" width="1/1" tablet_text_alignment="default" phone_text_alignment="default" column_border_width="none" column_border_style="solid"][tabbed_section style="default" alignment="left"][/tabbed_section][/vc_column][/vc_row]
```

INFORMACIÓN ADICIONAL

COTECNO