

## MÁQUINA AUTOMÁTICA DE PRUEBA DE FLEXIÓN



**SKU:** N / A | **Categorías:** [Cemento](#) | **Etiquetas:** [12390-5](#), [12390-6](#), [1340](#), [ASTM C293](#), [ASTM C496](#), [ASTM C78](#), [BS 1881](#), [EN 1338](#)

## GALERÍA DE IMÁGENES



## DESCRIPCIÓN DEL PRODUCTO

[vc\_row type="in\_container" full\_screen\_row\_position="middle" column\_margin="default" scene\_position="center" text\_color="dark" text\_align="left" overlay\_strength="0.3" shape\_divider\_position="bottom" bg\_image\_animation="none"][vc\_column column\_padding="no-extra-padding" column\_padding\_position="all" background\_color\_opacity="1" background\_hover\_color\_opacity="1" column\_link\_target="\_self" column\_shadow="none" column\_border\_radius="none" width="1/1" tablet\_width\_inherit="default" tablet\_text\_alignment="default" phone\_text\_alignment="default" overlay\_strength="0.3" column\_border\_width="none" column\_border\_style="solid" bg\_image\_animation="none"][tabbed\_section style="default" alignment="left" spacing="default" tab\_color="Accent-Color"][/tabbed\_section][[/vc\_column][[/vc\_row]

## INFORMACIÓN ADICIONAL

COTECNO