

MÁQUINA DE PRUEBA TRIAXIAL, SISTEMA DE PRUEBA UU



SKU: N / A | **Categorías:** [caminos y carreteras](#) |

DESCRIPCIÓN DEL PRODUCTO

I am text block. Click edit button to change this text. Lorem ipsum dolor sit amet, consectetur adipiscing elit. Ut elit tellus, luctus nec ullamcorper mattis, pulvinar dapibus leo.

- [Características](#)
- [Especificaciones técnicas](#)
- [Accesorios/ Respuestas](#)

I am text block. Click edit button to change this text.

[bg#1e73be;c#ffffff]Product Code	[bg#1e73be;c#ffffff]
Product Name	Triaxial Test Machine
Test speed (mm/mjn)	0,0001 - 9,9999
Capacity (kN)	5
Dimensions (cm)	50x50x135
Weight (kg)	135
Power supply	220 V, 50-60 Hz, 1 ph

[bg#1e73be;c#ffffff]Product Code	[bg#1e73be;c#ffffff] Product Name	[bg#1e73be;c#ffffff] Dimensions (cm)	[bg#1e73be;c#ffffff] Weight (kg)
	Triaxial Cell for 0 38 and 0 50 mm samples	16x16x40	4.5
	Triaxial Cell for 0 70 and 0 100 mm samples	21x21x55	12

[bg#1e73be;c#ffffff]Product Code	[bg#1e73be;c#ffffff]Product Name
	Triaxial Testing Frame
	Load Cell, 5 kN capacity
	Displacement Sensor, 25 x 0,01 mm
	Digital Readout and Control Unit

[bg#1e73be;c#ffffff]Product Code	[bg#1e73be;c#ffffff]Product Name
	Triaxial Cell for 0 38 and 0 50 mm samples
	Triaxial Cell for 0 70 and 0 100 mm samples
	Analog Manometer
	Digital Manometer (Optional)
	Air and Water Constant Pressure System
	Software to Perform UU Triaxial Tests
	De-Airing Water Tank, 7 lt
	Plastic Hose, 0 8 mm x 6 m

[bg#1e73be;c#ffffff]Product Name	[bg#1e73be;c#ffffff]Product Code	[bg#1e73be;c#ffffff]Product Code	[bg#1e73be;c#ffffff]Product Code	[bg#1e73be;c#ffffff]Product Code
Sample Diameter (mm)	38	50	70	100
Base Adaptor				
Porous Top Cap				

Nylon Tubing for Drainage
 Pair of Porous Discs
 Rubber Membrane
 Membrane Placing Tool
 (Strecher)
 O Ring (Pack of 10)
 O Ring Placing Tool
 Lateral Filter Paper (Pack of
 50)
 Filter Paper Discs (Pack of
 100)
 Plastic Discs (Pack of 2)

[bg#1e73be;c#ffffff]Product Name	[bg#1e73be;c#ffffff]Code	[bg#1e73be;c#ffffff]Code	[bg#1e73be;c#ffffff]Code	[bg#1e73be;c#ffffff]Code
Sample Diameter (mm)	38	50	70	100

Split Sand Former
 Split Mould
 Cutter
 Aluminum Dolly

[bg#1e73be;c#ffffff]Code	[bg#1e73be;c#ffffff]Name	[bg#1e73be;c#ffffff]Dimensions (cm)	[bg#1e73be;c#ffffff]Weight (kg)	[bg#1e73be;c#ffffff]Power Supply
	Analog Manometer	-	-	-
	Digital Manometer	-	-	-
	Air and Water Constant Pressure Unit	30x25x25	7.5	220-240V, 50-60Hz, 1ph

INFORMACIÓN ADICIONAL

COTECNO