

MONITOR SEESNAKE DVDPAK2



SKU: N / A | **Categorías:** [Desagües y alcantarillado](#), [Diagnóstico](#), [Ensayos no destructivos](#), [Inspección por vídeo de desagüe y alcantarillado](#), [Inspección Y Localización](#), [Monitores y grabadoras](#) | **Etiquetas:** [Ridgid](#)

GALERÍA DE IMÁGENES



DESCRIPCIÓN DEL PRODUCTO

[vc_row type="in_container" full_screen_row_position="middle" scene_position="center" text_color="dark" text_align="left" overlay_strength="0.3"] [vc_column column_padding="no-extra-padding" column_padding_position="all" background_color_opacity="1" background_hover_color_opacity="1" column_shadow="none" width="1/2" tablet_text_alignment="default" phone_text_alignment="default" column_border_width="none" column_border_style="solid"] [image_with_animation image_url="15897" alignment="" animation="Fade In" box_shadow="none" max_width="100%"] [vc_column] [vc_column column_padding="no-extra-padding" column_padding_position="all" background_color_opacity="1" background_hover_color_opacity="1" column_shadow="none" width="1/2" tablet_text_alignment="default" phone_text_alignment="default" column_border_width="none" column_border_style="solid"] [vc_column_text]

Monitor de cámara de inspección SeeSnake® DVDPak2

El monitor SeeSnake DVDPak2 le permite monitorear y grabar de manera fiable las inspecciones en las condiciones más extremas.

[vc_column_text] [vc_column] [vc_row] [vc_row type="in_container" full_screen_row_position="middle" scene_position="center" text_color="dark" text_align="left" overlay_strength="0.3"] [vc_column column_padding="no-extra-padding" column_padding_position="all" background_color_opacity="1" background_hover_color_opacity="1" column_shadow="none" width="1/1" tablet_text_alignment="default" phone_text_alignment="default" column_border_width="none" column_border_style="solid"]

[vc_column] [vc_row] [vc_row type="in_container" full_screen_row_position="middle" scene_position="center" text_color="dark" text_align="left" overlay_strength="0.3"] [vc_column column_padding="no-extra-padding" column_padding_position="all" background_color_opacity="1" background_hover_color_opacity="1" column_shadow="none" width="1/1" tablet_text_alignment="default" phone_text_alignment="default" column_border_width="none" column_border_style="solid"] [tabbed_section style="default" alignment="left"] [vc_column] [vc_row]

INFORMACIÓN ADICIONAL

COTECNO