

MUESTRA



SKU: N / A | Categorías: [Dispositivos varios](#), [Thies Clima](#) |

DESCRIPCIÓN DEL PRODUCTO

```
[vc_row type="in_container" full_screen_row_position="middle" column_margin="default" scene_position="center"
text_color="dark" text_align="left" overlay_strength="0.3" shape_divider_position="bottom"
bg_image_animation="none"][vc_column column_padding="no-extra-padding" column_padding_position="all"
background_color_opacity="1" background_hover_color_opacity="1" column_link_target="_self" column_shadow="none"
column_border_radius="none" width="1/1" tablet_width_inherit="default" tablet_text_alignment="default"
phone_text_alignment="default" overlay_strength="0.3" column_border_width="none" column_border_style="solid"
bg_image_animation="none"][vc_column_text]template[/vc_column_text][vc_row_inner column_margin="default"
text_align="left" css=".vc_custom_1597668708409{border-radius: 2px !important;}][vc_column_inner
column_padding="no-extra-padding" column_padding_position="all" background_color="#9492ff"
background_color_opacity="1" background_hover_color_opacity="1" font_color="ffffff" column_shadow="none"
column_border_radius="none" column_link_target="_self" width="1/4" tablet_width_inherit="default"
overlay_strength="0.3" column_border_width="none" column_border_style="solid"
bg_image_animation="none"][vc_column_text]
```

Imagen

```
[/vc_column_text][vc_column_inner][vc_column_inner column_padding="no-extra-padding" column_padding_position="all"
background_color="#9492ff" background_color_opacity="1" background_hover_color_opacity="1" font_color="ffffff"
column_shadow="none" column_border_radius="none" column_link_target="_self" width="1/4"
tablet_width_inherit="default" overlay_strength="0.3" column_border_width="none" column_border_style="solid"
bg_image_animation="none"][vc_column_text]
```

Nombre del Producto

```
[/vc_column_text][vc_column_inner][vc_column_inner column_padding="no-extra-padding" column_padding_position="all"
background_color="#9492ff" background_color_opacity="1" background_hover_color_opacity="1" font_color="ffffff"
column_shadow="none" column_border_radius="none" column_link_target="_self" width="1/2"
tablet_width_inherit="default" overlay_strength="0.3" column_border_width="none" column_border_style="solid"
bg_image_animation="none"][vc_column_text]
```

Descripción corta

```
[/vc_column_text][vc_column_inner][vc_row_inner][vc_row_inner column_margin="default"
text_align="left"][vc_column_inner column_padding="no-extra-padding" column_padding_position="all"
background_color_opacity="1" background_hover_color_opacity="1" column_shadow="none"
column_border_radius="none" column_link_target="_self" width="1/4" tablet_width_inherit="default"
overlay_strength="0.3" column_border_width="none" column_border_style="solid"
bg_image_animation="none"][image_with_animation image_url="138363" alignment="center" animation="Fade In"
hover_animation="none" border_radius="none" box_shadow="none" image_loading="default" max_width="100%"
max_width_mobile="default"][/vc_column_inner][vc_column_inner column_padding="no-extra-padding"
column_padding_position="all" background_color_opacity="1" background_hover_color_opacity="1"
column_shadow="none" column_border_radius="none" column_link_target="_self" width="1/4"
tablet_width_inherit="default" overlay_strength="0.3" column_border_width="none" column_border_style="solid"
bg_image_animation="none"][vc_column_text]
```

LED de pantalla de viento

4.3250.xx.0xx[/vc column text][vc column inner][vc column inner column padding="no-extra-padding"

```
column_padding_position="all" background_color_opacity="1" background_hover_color_opacity="1"
column_shadow="none" column_border_radius="none" column_link_target="_self" width="1/2"
tablet_width_inherit="default" overlay_strength="0.3" column_border_width="none" column_border_style="solid"
bg_image_animation="none"][/vc_column_text]Indicador digital para la visualización de la velocidad y dirección del viento
para sensores con interfaces digitales.[/vc_column_text][nectar_cta btn_style="see-through" heading_tag="h6"
button_color="default" link_type="new_tab" alignment="left" display="block" link_text="Leer más"
url="http://test.cotecno.cl/nuestros-productos/led-de-pantalla-de-viento"/][vc_column_inner][vc_row_inner]
```

```
[vc_row_inner column_margin="default" text_align="left"][/vc_column_inner column_padding="no-extra-padding"
column_padding_position="all" background_color_opacity="1" background_hover_color_opacity="1"
column_shadow="none" column_border_radius="none" column_link_target="_self" width="1/4"
tablet_width_inherit="default" overlay_strength="0.3" column_border_width="none" column_border_style="solid"
bg_image_animation="none"][/vc_column_inner][image_with_animation image_url="138363" alignment="center" animation="Fade In"
hover_animation="none" border_radius="none" box_shadow="none" image_loading="default" max_width="100%"
max_width_mobile="default"][/vc_column_inner][vc_column_inner column_padding="no-extra-padding"
column_padding_position="all" background_color_opacity="1" background_hover_color_opacity="1"
column_shadow="none" column_border_radius="none" column_link_target="_self" width="1/4"
tablet_width_inherit="default" overlay_strength="0.3" column_border_width="none" column_border_style="solid"
bg_image_animation="none"][/vc_column_text]
```

LED de pantalla de viento

```
4.3251.xx.0xx[/vc_column_text][vc_column_inner][vc_column_inner column_padding="no-extra-padding"
column_padding_position="all" background_color_opacity="1" background_hover_color_opacity="1"
column_shadow="none" column_border_radius="none" column_link_target="_self" width="1/2"
tablet_width_inherit="default" overlay_strength="0.3" column_border_width="none" column_border_style="solid"
bg_image_animation="none"][/vc_column_text]templateInstrumento de visualización digital que indica la velocidad y
dirección del viento con interfaces digitales.
```

- Versión de envío

```
[/vc_column_text][nectar_cta btn_style="see-through" heading_tag="h6" button_color="default" link_type="new_tab"
alignment="left" display="block" link_text="Leer más"
url="http://test.cotecno.cl/nuestros-productos/led-de-pantalla-de-viento-4"/][vc_column_inner][vc_row_inner]
```

```
[vc_row_inner column_margin="default" text_align="left"][/vc_column_inner column_padding="no-extra-padding"
column_padding_position="all" background_color_opacity="1" background_hover_color_opacity="1"
column_shadow="none" column_border_radius="none" column_link_target="_self" width="1/4"
tablet_width_inherit="default" overlay_strength="0.3" column_border_width="none" column_border_style="solid"
bg_image_animation="none"][/vc_column_inner][image_with_animation image_url="138363" alignment="center" animation="Fade In"
hover_animation="none" border_radius="none" box_shadow="none" image_loading="default" max_width="100%"
max_width_mobile="default"][/vc_column_inner][vc_column_inner column_padding="no-extra-padding"
column_padding_position="all" background_color_opacity="1" background_hover_color_opacity="1"
column_shadow="none" column_border_radius="none" column_link_target="_self" width="1/4"
tablet_width_inherit="default" overlay_strength="0.3" column_border_width="none" column_border_style="solid"
bg_image_animation="none"][/vc_column_text]
```

LED de pantalla de viento

```
4.3250.xx.1xx[/vc_column_text][vc_column_inner][vc_column_inner column_padding="no-extra-padding"
column_padding_position="all" background_color_opacity="1" background_hover_color_opacity="1"
```

```
column_shadow="none" column_border_radius="none" column_link_target="_self" width="1/2"
tablet_width_inherit="default" overlay_strength="0.3" column_border_width="none" column_border_style="solid"
bg_image_animation="none"][vc_column_text]Indicador digital para la visualización de la velocidad y dirección del viento
para sensores con interfaces analógicas.[/vc_column_text][nectar_cta btn_style="see-through" heading_tag="h6"
button_color="default" link_type="new_tab" alignment="left" display="block" link_text="Leer más"
url="http://test.cotecno.cl/nuestros-productos/led-de-pantalla-de-viento-2/"][/vc_column_inner][vc_row_inner]
```

```
[vc_row_inner column_margin="default" text_align="left"][vc_column_inner column_padding="no-extra-padding"
column_padding_position="all" background_color_opacity="1" background_hover_color_opacity="1"
column_shadow="none" column_border_radius="none" column_link_target="_self" width="1/4"
tablet_width_inherit="default" overlay_strength="0.3" column_border_width="none" column_border_style="solid"
bg_image_animation="none"][image_with_animation image_url="138363" alignment="center" animation="Fade In"
hover_animation="none" border_radius="none" box_shadow="none" image_loading="default" max_width="100%"
max_width_mobile="default"][/vc_column_inner][vc_column_inner column_padding="no-extra-padding"
column_padding_position="all" background_color_opacity="1" background_hover_color_opacity="1"
column_shadow="none" column_border_radius="none" column_link_target="_self" width="1/4"
tablet_width_inherit="default" overlay_strength="0.3" column_border_width="none" column_border_style="solid"
bg_image_animation="none"][vc_column_text]
```

LED de pantalla de viento

```
4.3251.xx.1xx[/vc_column_text][vc_column_inner][vc_column_inner column_padding="no-extra-padding"
column_padding_position="all" background_color_opacity="1" background_hover_color_opacity="1"
column_shadow="none" column_border_radius="none" column_link_target="_self" width="1/2"
tablet_width_inherit="default" overlay_strength="0.3" column_border_width="none" column_border_style="solid"
bg_image_animation="none"][vc_column_text]Instrumento de visualización digital que indica la velocidad y la dirección del
viento con interfaces analógicas.
```

- Versión de envío

```
[/vc_column_text][nectar_cta btn_style="see-through" heading_tag="h6" button_color="default" link_type="new_tab"
alignment="left" display="block" link_text="Leer más"
url="http://test.cotecno.cl/nuestros-productos/led-de-pantalla-de-viento-5/"][/vc_column_inner][vc_row_inner]
```

```
[/vc_column][vc_row]
```

INFORMACIÓN ADICIONAL

COTECNO