

OLLA PARA FUNDIR



Código del Producto:

UTC-1050

Olla para Fundir de 3 lts., 220-240 V 50-60 Hz

UTC-1050/110

Olla para Fundir de 3 lts., 110 V 60 Hz

Estándares:

EN 12390-3, 12390-1, 12504-1; ASTM C31, C192, C617, C39,



C42; AASTHO T23, T126

La UTC-1050 olla para fundir es usada para fundir cabeceo de azufre. El aparato consiste de un contenedor de aluminio de 3 litros de capacidad en una camisa de acero, cubierta (tapa), y un sistema de calentamiento de control termostático para mantener la temperatura constante en el rango de ambiente a 200 °C.

Dimensiones	350x320x290 mm
Peso (aprox.)	9 kg
Potencia	600 W

SKU: N / A | **Categorías:** [Concreto](#), [Prensas de hormigón](#) |

VARIACIONES

Imagen	SKU	Descripción	SKU / Modelo
 A blue cylindrical melting pot with a silver metal rim and a white lid. It has a wooden handle on top and a control panel on the side with a dial and a power switch. A red power cord is attached to the bottom.	UTC-1050	Olla para Fundir de 3 lts., 220-240 V 50-60 Hz	Any SKU / Modelo
 A blue cylindrical melting pot, identical in design to the one above, with a silver metal rim, white lid, wooden handle, and control panel with a dial and power switch. A red power cord is attached to the bottom.	UTC-1050/110	Olla para Fundir de 3 lts., 110 V 60 Hz	Any SKU / Modelo

INFORMACIÓN ADICIONAL

COTECNO