


PLACAS DE PENSADO PULIDAS



[vc_row][vc_column][vc_column_text]Placas de prensado de acero inoxidable pulido para aplicaciones de laminado. (La imagen muestra los 3 tamaños diferentes disponibles) [/vc_column_text][vc_table],[b;align-center]Placas%20y%20secadores%20pulidos%20(para%20aplicaciones%20de%20laminado)[[14px]235020,[14px]Placa%20de%20acero%20inoxidable%20pulido%20con%20acabado%20de%20espejo%20pulido%20n.%20%20%20C2%B0%208%20en%20un%20lado%20y%20acabado%20de%202-3%20micro%20pulgadas%2C%206%20%22x%206%22%20x%20.03%20%22de%20espesor[[14px]235021,[14px]Placa%20de%20acero%20inoxidable%20pulido%20con%20acabado%20de%20espejo%20pulido%20%23%208%20en%20un%20lado%20y%20acabado%20de%202-3%20micro-pulgadas%2C%209%20%22x%209%22%20x%20.03%20%22de%20espesor[[14px]235022,[14px]Placa%20de%20acero%20inoxidable%20pulido%20con%20acabado%20de%20espejo%20pulido%20%23%208%20en%20un%20lado%20y%20acabado%20de%202-3%20micro-pulgadas%2C%209%20%22x%2012%22%20x%20.03%20%22de%20espesor[[14px]235023,[14px]Placa%20de%20acero%20inoxidable%20pulido%20con%20acabado%20de%20espejo%20pulido%20%23%208%20en%20un%20lado%20y%20acabado%20de%202-3%20micro-pulgadas%2C%2012%20%22x%2012%22%20x%20.03%20%22de%20espesor[[14px]823003,[14px]Papel%20secante%20protector%2C%206%20%22x%206%22[[14px]823012,[14px]Papel%20secante%20protector%2C%209%20%22x%209%22[[14px]823005,[14px]Papel%20secante%20protector%2C%209%20%22x%2012%22[[14px]823001,[14px]Papel%20secante%20protector%2C%2012%20%22x%2012%22[/vc_table][vc_column][vc_row]

SKU: N / A | **Categorías:** [Equipos de prueba y procesamiento](#) |

INFORMACIÓN ADICIONAL

COTECNO