

PLATO CALIENTE - BE-PLATC-6A



Código SKU: B-01-29-000700-0201

SKU: B-01-29-000700-0201 | **Categorías:** [Sin categoría](#) |

GALERÍA DE IMÁGENES



DESCRIPCIÓN DEL PRODUCTO

- [DESCRIPCION](#)
- [PARAMETROS TECNICOS](#)
- [CERTIFICADO](#)

1. Aluminun Placa caliente, temperatura de la superficie uniforme.
2. Heating Up Fast and Uniform, la potencia de calefacción está segura ajustable
3. La placa calientedigital tiene las más funciones de la siguiente manera: La pantalla digital puede leer la temperatura más claramente.

Modelo	BE-PlatC-5A / 5C	BE-PlatC-6A / 6C	BE-PlatC-7A / 7C	BE-PlatC-8A / 8C	BE-PlatC-9A / 9C	
Código SKU	B-01-29-0007000-0200 / B-01-29-0007000-0205	B-01-29-0007000-0201 / B-01-29-0007000-0206	B-01-29-0007000-0202 / B-01-29-0007000-0207	B-01-29-0007000-0203 / B-01-29-0007000-0208	B-01-29-0007000-0204 / B-01-29-0007000-0209	
Funcion	Tiempo de trabajo		Continuo			
	TEMP MAX (°C)		350 °C			
	Concha exterior		Soldadura de placa de hierro, pulverización de superficie			
Estructura	Plato caliente		Tensas de aluminio			
	Modo de conducción		No			
	Poder de calefacción (W)	1200	1800	2000	2600	3000

Modelo	BE-PlatC-5A / 5C	BE-PlatC-6A / 6C	BE-PlatC-7A / 7C	BE-PlatC-8A / 8C	BE-PlatC-9A / 9C
Operación continua			sí		
Método de ajuste			Escala / digital		
Temporizador			No / digital		
Función de operación			No		
Sensor de temperatura			Modelo k		
Tamaño exterior (W * L * H) (cmetro)	30 * 30 * 18	35 * 45 * 18	40 * 40 * 18	35 * 60 * 18	40 * 60 * 18
Tamaño de embalaje(W * l * h) (cmetro)	34 * 37 * 22	42 * 50 * 22	45 * 47 * 22	42 * 65 * 22	47 * 65 * 22
tamaño (mm)	300 * 300	350 * 450	400 * 400	350 * 600	400 * 600
Carga de placa	20kg	30kg	30kg	38kg	40kg
Fuente de alimentación (50 / 60Hz)			220v		
NW / GW (kg)	6.2 / 7	8.4 / 9.6	8.5 / 9.8	11/13	12/14.2



Safenet Limited
 Deans Road, Darford, Kettering, Northants, NN14 4EG, U.K.
 Tel: +44 (0)1533 611111 Email: info@safenet.co.uk Website: www.safenet.co.uk

Certificate of Conformity

This is to certify that
Huanghua Faithful Import & Export Co., Ltd.
 Complex Building, Qinggong Home Garden, Changhua Road, Huanghua City, Hebei Province, China

Has had a range of Magnetic Dimensionalizers with regards to the Low Voltage Directive 2014/53/EU.

With reference to model **SH-2**

Manufactured by
Huanghua Faithful Instrument Co., Ltd.
 No. 7 Road, Baocun & Technology Zone, Huanghua City, Hebei Province, China

- The technical documentation supplied contains all the relevant information.
- Having verified that the appropriate tests have been conducted with regard to the EMC, representing the scope.
- The example has been manufactured in accordance with the technical documentation and may be used under the stipulated conditions.
- The standards and harmonized standards as the case may be, have been applied correctly.
- The example has conformity with the Provisions of Safety Objectives of the Low Voltage Directive 2014/53/EU.
- The technical documentation supplied contains all the information required to include the following models SH-2, SH-3B, SH-2C, SH-3, SH-3B, SH-3C, SH-4, SH-4A, SH-4B, SH-4C, SH-4, SH-4A, SH-4B, SH-4C, SH-4, SH-4A, SH-4B, SH-4C, SH-5, SH-5A, SH-5B, SH-5C, SH-5, SH-5A, SH-5B, SH-5C, SH-6, SH-6A, SH-6B, SH-6C, SH-6, SH-6A, SH-6B, SH-6C, SH-7, SH-7A, SH-7B, SH-7C, SH-7, SH-7A, SH-7B, SH-7C, SH-8, SH-8A, SH-8B, SH-8C, SH-9, SH-9A, SH-9B, SH-9C.

Certificate Number: 4987820119C, version 2
 Date: 06/03/2018

Signed for Safenet Limited

 Peter Mitchell
 Technical Manager




This document contains the property of Safenet Ltd and shall be returned to Safenet if requested. Safenet will assume full liability for compliance with the requirements of CE marking systems where the markings do not meet the CE mark.

INFORMACIÓN ADICIONAL

COTECNO