

## PLATO CALIENTE - BE-PLATC-9A



Código SKU: B-01-29-000700-0204

**SKU:** N / A | **Categorías:** [Sin categoría](#) |

## GALERÍA DE IMÁGENES



## DESCRIPCIÓN DEL PRODUCTO

- [DESCRIPCION](#)
- [PARAMETROS TECNICOS](#)
- [CERTIFICADO](#)

1. Aluminun Placa caliente, temperatura de la superficie uniforme.
2. Heating Up Fast and Uniform, la potencia de calefacción está segura ajustable
3. La placa calientedigital tiene las más funciones de la siguiente manera: La pantalla digital puede leer la temperatura más claramente.

Modelo	BE-PlatC-5A / 5C	BE-PlatC-6A / 6C	BE-PlatC-7A / 7C	BE-PlatC-8A / 8C	BE-PlatC-9A / 9C
Código SKU	B-01-29-0007000-0200	B-01-29-0007000-0201	B-01-29-0007000-0202	B-01-29-0007000-0203	B-01-29-0007000-0204
	/	/	/	/	/
	B-01-29-0007000-0205	B-01-29-0007000-0206	B-01-29-0007000-0207	B-01-29-0007000-0208	B-01-29-0007000-0209
Funcion			Continuo		
TEMP MAX (°C)			350 °C		
Concha exterior		Soldadura de placa de hierro, pulverización de superficie			
Estructura			Tensas de aluminio		
Modo de conducción			No		
Poder de calefacción (W)	1200	1800	2000	2600	3000

Modelo	BE-PlatC-5A / 5C	BE-PlatC-6A / 6C	BE-PlatC-7A / 7C	BE-PlatC-8A / 8C	BE-PlatC-9A / 9C
Operación continua			sí		
Método de ajuste			Escala / digital		
Temporizador			No / digital		
Función de operación			No		
Sensor de temperatura			Modelo k		
Tamaño exterior (W * L * H) (cmetro)	30 * 30 * 18	35 * 45 * 18	40 * 40 * 18	35 * 60 * 18	40 * 60 * 18
Tamaño de embalaje(W * l * h) (cmetro)	34 * 37 * 22	42 * 50 * 22	45 * 47 * 22	42 * 65 * 22	47 * 65 * 22
tamaño (mm)	300 * 300	350 * 450	400 * 400	350 * 600	400 * 600
Carga de placa	20kg	30kg	30kg	38kg	40kg
Fuente de alimentación (50 / 60Hz)			220v		
NW / GW (kg)	6.2 / 7	8.4 / 9.6	8.5 / 9.8	11/13	12/14.2



**Safenet Limited**  
 Deansfield Garage, Deansfield, Kettering, Northants, NN14 4EG, U.K.  
 Tel: +44 (0)1533 711111 Email: info@safenet.co.uk Website: www.safenet.co.uk

**Certificate of Conformity**

This is to certify that  
**Huanghua Faithful Import & Export Co., Ltd.**  
 Complex Building, Cloggery Homegarden, Changhua Road, Huanghua City, Hebei Province, China

Has had a range of Magnetic Dimensionalizers with regards to the Low Voltage Directive 2014/53/EU.

With reference to model **SH-2**

Manufactured by  
**Huanghua Faithful Instrument Co., Ltd.**  
 No. 7 Road, Baocun & Technology Zone, Huanghua City, Hebei Province, China

- The technical documentation supplied contains all the relevant information.
- Having verified that the appropriate tests have been conducted with regard to the EMC, representing the scope.
- The example has been manufactured in accordance with the technical documentation and may be used under the stipulated conditions.
- The standards and harmonized standards as the case may be, have been applied correctly.
- The example has conformity with the Provisions of Safety Objectives of the Low Voltage Directive 2014/53/EU.
- The technical documentation supplied contains all the information required to include the following models SH-2, SH-3B, SH-2C, SH-3, SH-3B, SH-3C, SH-4, SH-4A, SH-4B, SH-4C, SH-4, SH-4A, SH-4B, SH-4C, SH-4, SH-4A, SH-4B, SH-4C, SH-5, SH-5A, SH-5B, SH-5C, SH-5, SH-5A, SH-5B, SH-5C, SH-6, SH-6A, SH-6B, SH-6C, SH-6, SH-6A, SH-6B, SH-6C, SH-7, SH-7A, SH-7B, SH-7C, SH-7, SH-7A, SH-7B, SH-7C, SH-8, SH-8A, SH-8B, SH-8C, SH-9, SH-9A, SH-9B, SH-9C.

Certificate Number: 4987820119c, version 2  
 Date: 06/03/2018

Signed for Safenet Limited  
  
 Peter Mitchell  
 Technical Manager




This document contains the property of Safenet Ltd and shall be returned to Safenet if requested. Safenet will assume full liability for compliance of the manufacturing and supply systems where the message is the best available.

## INFORMACIÓN ADICIONAL

COTECNO