

## SISTEMA DE INSPECCIÓN DE VÍDEO INDUSTRIAL SEESNAKE NANOREEL



**SKU:** N / A | **Categorías:** [Carretes y cámaras](#), [Desagües y alcantarillado](#), [Diagnóstico](#), [Ensayos no destructivos](#), [Inspección por vídeo de desagüe y alcantarillado](#), [Inspección Y Localización](#) | **Etiquetas:** [Ridgid](#)

## GALERÍA DE IMÁGENES



## DESCRIPCIÓN DEL PRODUCTO

[vc\_row type="in\_container" full\_screen\_row\_position="middle" scene\_position="center" text\_color="dark" text\_align="left" overlay\_strength="0.3"][vc\_column column\_padding="no-extra-padding" column\_padding\_position="all" background\_color\_opacity="1" background\_hover\_color\_opacity="1" column\_shadow="none" width="1/2" tablet\_text\_alignment="default" phone\_text\_alignment="default" column\_border\_width="none" column\_border\_style="solid"][tabbed\_section style="default" alignment="left"][/tabbed\_section][vc\_column column\_padding="no-extra-padding" column\_padding\_position="all" background\_color\_opacity="1" background\_hover\_color\_opacity="1" column\_shadow="none" width="1/2" tablet\_text\_alignment="default" phone\_text\_alignment="default" column\_border\_width="none" column\_border\_style="solid"]

### Sistema de inspección de vídeo SeeSnake® microReel

Tuberías de 1-1/2" a 4 / 5" (40 a 100 / 125 mm)\* hasta 100 pies (30 m). Supera codos de 90° en casi todas las tuberías de 2" (50 mm).

El sistema de inspección de vídeo microReel proporciona maniobrabilidad y tamaño reducido para inspección de conductos de pequeño diámetro y curvas cerradas.

\* 4" (100 mm) cuando se utiliza con una cámara de inspección microEXPLORER™ o micro CA-300. 5" (125 mm) cuando se utiliza con un monitor SeeSnake.

[vc\_column\_text][vc\_column][vc\_row][vc\_row type="in\_container" full\_screen\_row\_position="middle" scene\_position="center" text\_color="dark" text\_align="left" overlay\_strength="0.3"][vc\_column column\_padding="no-extra-padding" column\_padding\_position="all" background\_color\_opacity="1" background\_hover\_color\_opacity="1" column\_shadow="none" width="1/1" tablet\_text\_alignment="default" phone\_text\_alignment="default" column\_border\_width="none" column\_border\_style="solid"]

[vc\_column][vc\_row][vc\_row type="in\_container" full\_screen\_row\_position="middle" scene\_position="center" text\_color="dark" text\_align="left" overlay\_strength="0.3"][vc\_column column\_padding="no-extra-padding" column\_padding\_position="all" background\_color\_opacity="1" background\_hover\_color\_opacity="1" column\_shadow="none" width="1/1" tablet\_text\_alignment="default" phone\_text\_alignment="default" column\_border\_width="none" column\_border\_style="solid"]

alignment="left"/>[tabbed\_section]/[vc\_column]/[vc\_row]

COTECNO

## INFORMACIÓN ADICIONAL

COTECNO