


**TAMIZ DE 8" DE ACERO INOXIDABLE CON CERTIFICADO ASTM E11 INTERNACIONAL - MARCO INOXIDABLE / MALLA INOXIDABLE ALTURA COMPLETA (2 "- 50 MM)**



**SKU:** N / A | **Categorías:** [Agregados](#), [Tamices ASTM](#) |

## VARIACIONES

Imagen	SKU	Descripción	Tamiz - Apertura nominal (mm)	Tamiz - Apertura nominal (um)	Diametro del tamiz (pulgadas)
	B-01-02-01-0100		63	Any Tamiz - Apertura nominal (um)	Any Diametro del tamiz (pulgadas)
	B-01-02-01-0200		50	Any Tamiz - Apertura nominal (um)	Any Diametro del tamiz (pulgadas)
	B-01-02-01-0300		37.5	Any Tamiz - Apertura nominal (um)	Any Diametro del tamiz (pulgadas)
	B-01-02-01-0400		25	Any Tamiz - Apertura nominal (um)	Any Diametro del tamiz (pulgadas)
	B-01-02-01-0500		19	Any Tamiz - Apertura nominal (um)	Any Diametro del tamiz (pulgadas)
	B-01-02-01-0600		12.5	Any Tamiz - Apertura nominal (um)	Any Diametro del tamiz (pulgadas)

Imagen	SKU	Descripción	Tamiz - Apertura nominal (mm)	Tamiz - Apertura nominal (um)	Diámetro del tamiz (pulgadas)
	B-01-02-01-0700	3.35	Any Tamiz - Apertura nominal (um)	Any Diámetro del tamiz (pulgadas)	

COTECNO

## DESCRIPCIÓN DEL PRODUCTO

### Especificaciones Técnicas

SKU	Descripción / Tamaño de apertura nominal (mm)
B-01-02-01-0100	Tamiz 2 1/2' (63 mm) - no certificable
B-01-02-01-0200	Tamiz 2' (50 mm) - no certificable
B-01-02-01-0300	Tamiz 1 1/2' (37.5 mm) - no certificable
B-01-02-01-0400	Tamiz 1' (25 mm) - no certificable
B-01-02-01-0500	Tamiz 3/4' (19 mm) - no certificable
B-01-02-01-0600	Tamiz 1/2' (12.5 mm) - no certificable
B-01-02-01-0700	Tamiz 3/8' (9.5 mm) - no certificable
B-01-02-01-0800	Tamiz 1/4' (6.3 mm) - no certificable
B-01-02-01-0900	Tamiz #4 (4.75 mm) - no certificable
B-01-02-01-1000	Tamiz #6 (3.35 mm) no certificable
B-01-02-01-1100	Tamiz #10 (2 mm) - no certificable
B-01-02-01-1200	Tamiz #12 (1.7 mm) certificado (calibracion opcional)
B-01-02-01-1300	Tamiz #14 (1.40 mm) - no certiifiable
B-01-02-01-1400	Tamiz #16 (1.18 mm) certificado (calibracion opcional)
B-01-02-01-1500	Tamiz #20 (850 um) - no certificable

SKU	Descripción / Tamaño de apertura nominal (mm)
B-01-02-01-1500	Tamiz #20 (850 um) - no certificable
B-01-02-01-1600	Tamiz #30 (600 um) certificado (calibracion opcional)
B-01-02-01-1700	Tamiz #40 (425 um) - no certificable
B-01-02-01-1800	Tamiz #50 (300 um) certificado (calibracion opcional)
B-01-02-01-1900	Tamiz #60 (250 um) certificado (calibracion opcional)
B-01-02-01-2000	Tamiz #100 (150 um) certificado (calibracion opcional)
B-01-02-01-2100	Tamiz #200 (75 um) certificado (calibracion opcional)
B-01-02-01-2101	Tamiz #200 (75 um) (Lavado)

## INFORMACIÓN ADICIONAL

COTECNO